






THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

REFERENCE MATING INTERFACE PATTERN:
1,27 STAGGERED PITCH x 1,5 ROW-DISTANCE.





NOTES:


- 1 TAPE FOR VACUUM P&P ONLY FOR DASHNUMBERS 7- /8- /9-
- 2 FOR PACKAGING SEE SHEET 2 OF 2
- 3 WITHOUT VACUUM TAPE.
- 4 CORING-OUTS FOR MANUFACTURING PURPOSE ONLY.
SHAPE MAY VARY, BUT IS NOT FUNCTIONAL FOR THE APPLICATION.
- 5 SHOWN IS A 10 POSITION CONNECTOR.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	S4	PACKAGING BLISTER MATERIAL CHANGE	08MAY2015	NV	PS

PART NUMBER VAC. TAPE. 1	PART REV	PART NUMBER 3	PART REV	NR.OF POS. "n"	"A"	"B" MAX.
7-188275-4	U	0-188275-4	U	4	3,81	7,1
7-188275-6	U	0-188275-6	U	6	6,35	9,7
7-188275-8	U	0-188275-8	U	8	8,89	12,2
8-188275-0	U	1-188275-0	U	10	11,43	14,7
8-188275-2	U	1-188275-2	U	12	13,97	17,3
8-188275-4	U	1-188275-4	U	14	16,51	19,8
8-188275-6	U	1-188275-6	U	16	19,05	22,4
8-188275-8	V	1-188275-8	V	18	21,59	24,9
9-188275-0	U	2-188275-0	U	20	24,13	27,5



3	PICK & PLACE TAPE	KAPTON	AMBER TRANSPARENT
2	FEMALE HOUSING	POLYAMIDE 4/6,GF	RED
1	FEMALE CONTACT	PHOSPHOR BRONZE	TIN OVER NICKEL
ITEM NO.	COMPONENT DESCRIPTION	MATERIAL	FINISH / COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. GOSSELINK		 TE Connectivity					
DIMENSIONS: mm		CHK -							
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONNECTOR, FEMALE-ON-BOARD TOP-ENTRY, SMD, Micro-MaTch					
		0 PLC ±-							
		1 PLC ±-							
		2 PLC ±-							
3 PLC ±-		APVD -		SIZE A3					
4 PLC ±-		PRODUCT SPEC 108-19052					CAGE CODE 00779		
ANGLES ±-		APPLICATION SPEC 114-13318							
MATERIAL SEE TABLE		FINISH SEE TABLE		RESTRICTED TO -					
				WEIGHT -					
				CUSTOMER DRAWING					
				SCALE 5:1					
				SHEET 1 OF 2					
				REV S4					

RECOMMENDED PC-BOARD
PAD-LAYOUT TOP VIEW

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD





SEE SHEET 1

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm

TAPE WIDTH
24 mm



7-188275-4

7-188275-6

7-188275-8

8-188275-0

4 POSITION

6 POSITION

8 POSITION





10 POSITION

0-188275-4

0-188275-6

0-188275-8

1-188275-0








TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm

TAPE WIDTH 44 mm



8-188275-2

8-188275-4

8-188275-6

8-188275-8

9-188275-0

12 POSITION

14 POSITION

16 POSITION

18 POSITION

20 POSITION






1-188275-2

1-188275-4

1-188275-6

1-188275-8

2-188275-0



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

M. GOSSELINK

CHK

-

APVD

-

PRODUCT SPEC

108-19052

APPLICATION SPEC

114-13318


WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.1
2 PLC ±0.05
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

MATERIAL

-



TE Connectivity

CONNECTOR,
FEMALE-ON-BOARD TOP-ENTRY,
SMD, Micro-MaTch

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-188275

-

SCALE

1:1

SHEET

2

OF

2

REV

S4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-188275-4](#)