






P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE APPLICATION SPECIFICATION

①	MATERIAL HOUSING	: GRAY GLASSFILLED POLYESTER UL-RATING V0
	CONTACT	: PHOSPHORBRONZE
②	GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27μm NICKEL MIN. AND ACTION PIN: 0,5μm TIN-LEAD MIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.	
③	CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.	
④	CONNECTOR ASSEMBLY WITH LATCH HINGE FOR CABLE CONNECTOR.	
⑤	CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE	
⑥	PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.	

		1-188748-1 
		188748-1
CONTACT FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.V.d.HEIJDEN 15DEC97		tyco Electronics		Tyco Electronics Corporation	
		CHK D. TRUREN 15DEC97				s-Hertogen Bosch, Netherlands,	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME Z-PACK 2MM HM TYPE C 55 POS. RIGHT ANGLE MALE CONNECTOR ASSEMBLY			
		APVD F.V.KONINGSBRUGGE - PRODUCT SPEC					
		APPLICATION SPEC 114-19029				SIZE	
		WEIGHT -				CAGE CODE	
MATERIAL -		FINISH -		DRAWING NO A2 00779 C-188748		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE		NTS	
				SHEET		1 OF 1	
				REV		D1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[188748-1](#)