



## REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECR-19-016494	24OCT2019	F.Z	R.B





1. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
2. ALTERNATIVE LOGO MARK FOR DIFFERENT DIE.
3. ALTERNATIVE ID MARK, WITH "■" OR NO MARK.

AS SHOWN: 1903116-2

1	COPPER ALLOY: FINISH; CONTACT AREA Au 0.38umMIN, OVER Ni 1.27umMIN	1903116-2
	MATERIAL	PART NO

© 2019 TE Connectivity. All Rights Reserved.

DIMENSIONS:		DWN M. MAEBASHI	11APR2006	MATERIAL		FINISH	
mm		CHK T. KUDO	11APR2006	<div>TE Connectivity</div>			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MITSUGI	11APR2006				
± 0.3, ± 3°		PRODUCT SPEC		NAME DYNAMIC D1000 SERIES TAB CONTACT Au, M-TYPE L/P			
0 PLC ±		108-78268					
1 PLC ±		APPLICATION SPEC		SIZECAGE CODEDRAWING NORESTRICTED TO			
2 PLC ±		114-5377					
3 PLC ±		WEIGHT		A400779C-1903116			
4 PLC ±		0.075 g					
ANGLES ±		CUSTOMER DRAWING		SCALE7:1			
				SHEET1 OF1			
				REV C			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1903116-2](#)