






REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECR-19-016494	24OCT2019	F.Z	R.B



AS SHOWN: 1903121-1

△ PRE-TIN COPPER ALLOY

1903121-1

MATERIAL

PART NO

WIRE RANGE

mm²

AWG#28-#22

0.08~0.38

INSULATION DIA

Ø1.08~Ø1.9



TE Connectivity

NAME

DYNAMIC D1000 SERIES
TAB CONTACT TIN-PLATE L-TYPE REEL

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1903121

SCALE

10:1

SHEET

OF

REV

C

1. APPLICATION TAB-HSG IS APPLIED TO THE PRODUCT OF 2.5mm PITCH OR MORE OF DYNAMIC D1000 SERIES. 2.0mm PITCH CANNOT BE USED.

2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE.

THEY DON'T SHOW DETAILS.


△3 ALTERNATIVE LOGO MARK FOR DIFFERENT DIE.

△4 ALTERNATIVE ID MARK, WITH "□" OR NO MARK.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS

OTHERWISE SPECIFIED:

±0.3, ±3°

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

MATERIAL

material_2

DWN

M. MAEBASHI

CHK

T. KUDO

APVD

D. MITSUGI

PRODUCT SPEC

108-78298

APPLICATION SPEC

114-5377

WEIGHT

0.128 g

CUSTOMER DRAWING

26APR2006

26APR2006

26APR2006

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1903121-1](#)