


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J			C	REVISED PER ECR-10-017569	26AUG2010	HMR	T.M


D



20POS(X-KEY): 1-1903130-0

CAVITY MARK
(ALPHABET: CAPITAL LETTER)

C



CIRCUIT NO


KEYING: X

CIRCUIT NO

LOGO MARK

SERIES CODE

B



ROW ID
(BOTH SIDE)


1. MATERIAL: GLASS FILED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
3. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".

1. 材料: ガラス入り熱可塑性ポリエステル樹脂(94V-0), 色: 黒
2. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。
3. Y KEY形状は、X KEY形状と左右対称

AS SHOWN 20POS(X-KEY) : 1-1903130-0

20	Y	9	22.5	26.0	27.6	26.2	2-1903130-0
20	X	9	22.5	26.0	27.6	26.2	1-1903130-0
12	Y	5	12.5	16.0	17.6	16.2	2-1903130-6
12	X	5	12.5	16.0	17.6	16.2	1-1903130-6
8	Y	3	7.5	11.0	12.6	11.2	2-1903130-4
8	X	3	7.5	11.0	12.6	11.2	1-1903130-4
6	Y	2	5.0	8.5	10.1	8.7	2-1903130-3
6	X	2	5.0	8.5	10.1	8.7	1-1903130-3
4	X	1	2.5	6.0	7.6	6.2	1-1903130-2
POS	KEY	n	A	B	C	D	PART NO

A



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				DWN M. MAEBASHI 11APR2006	Tyco Electronics Corporation Kawasaki, Japan		
DIMENSIONS: 単位: 純				CHK T. KUDO 11APR2006			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±3°				APVD D. MITSUGI 11APR2006	NAME DYNAMIC D1200D 2.5mm PITCH TAB HSG, FREE HANGING TYPE 4-20 POS		
0-PLC ±				PRODUCT SPEC 108-78268, 78298			
1-PLC ±				APPLICATION SPEC 取付適用規格	SIZE A200779		
2-PLC ±				114-5377			
3-PLC ±				WEIGHT	DRAWING NO C-1903130		
4-PLC ±				CUSTOMER DRAWING			
ANGLES FINISH 仕上				SCALE 5:1	SHEET 1 OF 2		

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2006

© COPYRIGHT 2006

BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

J

REVISIONS

REV

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1 OF 2

C

B

2.5Xn=A

12POS(X-KEY): I-1903130-6

C

B

2.5Xn=A

8POS(X-KEY): I-1903130-4

C

B

2.5Xn=A

6POS(X-KEY): I-1903130-3

C

B

2.5Xn=A

4POS(X-KEY): I-1903130-2

9

X

↓

D1200

6

5

4

3

2

1

D

4

X

↓

D1200

4

3

2

1

D

3

X

↓

D1200

3

2

1

D

2

X

↓

D1200

2

1

D

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
単位: 純

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

MATERIAL 材料

FINISH 仕上

DWN
M. MAEBASHI 11APR2006

CHK
T. KUDO 11APR2006

APVD
D. MITSUGI 11APR2006

PRODUCT SPEC
108-78268, 78298

APPLICATION SPEC
取付適用規格
114-5377

WEIGHT

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation

Kawasaki, Japan

NAME 名称

DYNAMIC D1200D 2.5mm PITCH

TAB HSG, FREE HANGING TYPE

4-20 POS

SIZE 寸法

CAGE CODE 番号

DRAWING NO 番号

RESTRICTED TO

SCALE 尺度

5:1

SHEET 2 OF 2

REV C

1471-9 (2/09)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1903130-6](#)