




P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECR-19-011328	18JUL2019	K.T	E.I




SCALE 1:1



SEQUENTIAL CONTACT : ONLY CIRCUIT NO.1



SEQUENTIAL ITEM



RECOMMEND PC BOARD HOLE PATTERN : CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.6~2.4±0.1
推奨基板取付穴寸法 : コネクタ搭載面 (非累積公差)
PC基板厚 : 1.6~2.4±0.1

AS SHOWN : 1-1903328-4 (4POS: X-KEY)

4	3	19.05	31.05	35.05	29.05		Y	2-1903328-4 6-1903328-4
4	3	19.05	31.05	35.05	29.05		X	1-1903328-4 5-1903328-4
3	2	12.70	24.70	28.70	22.70		Y	2-1903328-3 6-1903328-3
3	2	12.70	24.70	28.70	22.70		X	1-1903328-3 5-1903328-3
2	1	6.35	18.35	22.35	16.35		Y	2-1903328-2
2	1	6.35	18.35	22.35	16.35		X	1-1903328-2
POS	n	A	B	C	D	KEY LOCATION	KEY	PART NUMBER


COMPANY LOGO

SERIES CODE

CIRCUIT NO

DATE CODE

HDR HSG




1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC
POLYESTER (94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY

2. FINISH (ALL OVER): NICKEL PL. 1.3μm MIN
3. FINISH (CONTACT AREA): GOLD PL. 0.38μm MIN AFTER 2
4. FINISH (CONTACT TAIL & RETENTION LEG): TIN PL. 2μm MIN AFTER 2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mm



MATERIAL
材料

material_2

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差 ±0.3, ±3°
0-PLC ±
1-PLC ±0.1
2-PLC ±0.01
3-PLC ±0.001
4-PLC ±0.0001
ANGLES ±

FINISH
仕上

finish_spec_2

DWN 23MAR2007

M. MAEBASHI

CHK 23MAR2007

T. KUDO

APVD 23MAR2007

D. MITSUGI

PRODUCT SPEC

製品規格

108-78182

APPLICATION SPEC

取付適用規格

114-5369

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME
名称 DYNAMIC D4200S 6.35mm PITCH
HDR ASSY (H-TYPE)
2-4POS

SIZE

CAGE CODE

DRAWING NO
番号

A300779

C-1903328

RESTRICTED TO

SCALE
尺度

2:1

SHEET

1 OF 1

REV

C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1903328-2](#)