

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

4

3

2

1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	ECR-15-008603	24JUN2015	KG	DW
	C1	ECR-19-015389	21OCT2019	LN	DW
	C2	ECO-20-009383	14JUL2020	LN	DW

CRIMP SLEEVE
MAT'L: NICKEL-SILVER ALLOY

WASHER
MAT'L: STAINLESS STEEL

SEAL
MAT'L: FLUOROSILICONE RUBBER

EXTENSION
MAT'L: SEE TABLE

BOOT
MAT'L: EPDM RUBBER

CRIMP SUPPORT
MAT'L: NICKEL-SILVER ALLOY

CRIMP SLEEVE
MAT'L: NICKEL-SILVER ALLOY

WASHER
MAT'L: STAINLESS STEEL

SEAL
MAT'L: FLUOROSILICONE RUBBER

EXTENSION
MAT'L: SEE TABLE

BOOT
MAT'L: EPDM RUBBER

RAL 4004
CLARET VIOLET

ALUMINUM ALLOY

5.7mm

2-1918931-0

RAL 3003
RUBY RED

ALUMINIUM ALLOY

6.2mm

1-1918931-8

5.7mm

1-1918931-7

3

7.5mm

1-1918931-6

6.7mm

1-1918931-5

6.0mm

1-1918931-4

5.5mm

1-1918931-3

5.0mm

1-1918931-2

4.2mm

1-1918931-1

3.6mm

1-1918931-0

3.2mm

1918931-9

3

7.5mm

1918931-8

6.7mm

1918931-7

6.0mm

1918931-6

5.5mm

1918931-5

5.0mm

1918931-4

4.2mm

1918931-3

3.6mm

1918931-2

3.2mm

1918931-1

BLACK

NICKEL
ALUMINUM
BRONZE

BLACK

ALUMINUM
ALLOY

BOOT
COLOR

EXTENSION
MATERIAL

MAXIMUM
CABLE DIAMETER

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
K. GLATFELTER
CHK
D. WERTMAN
APVD
D. WERTMAN

27OCT2006
02JUN2008
02JUN2008

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH
HARD ANODIZE
(AL ONLY)

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

NAME
CABLE ADAPTER KIT, PLUG,
PRO BEAM JR.

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-1918931

RESTRICTED TO
-

Customer Drawing

SCALE
3:1

SHEET
1

OF
1

REV
C2

1. PACKAGED LOOSE PIECE.

2. DIMENSIONS ARE FOR REFERENCE ONLY.

3

 FOR USE WITH Ø7.5mm BREAKOUT CABLE WITH Ø2.15mm
MAXIMUM JACKETED SUBUNITS.

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1918931-3](#)