




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	REV PER ECO-10-018478	15SEP2010	RG	DO
	M	REV PER ECO-17-013721	21DEC2017	RS	MZ



STYLE C
(STRIP)



STYLE A
(FEMALE)



1. FINISH - SILVER PLATE 500μINCHES MIN THK.
2. FINISH - NICKEL PLATE 40μINCHES MIN THK
3. FINISH - GOLD PLATE 10μINCHES MIN THK.
- 4 LENGTH TO BE 7.6 INCHES
- 5 LENGTH TO BE 10.8 INCHES
6. PLATING NOTES ARE TO BE INTERPRETED AS FOLLOWS: 1-2 AS 1 OVER 2.
- 7 PRODUCT SOLD BY THE FOOT.
- 8 LENGTH 9.2 INCHES
- 9 LENGTH 8.0 INCHES
- 10 LENGTH 11.9 INCHES
- 11 PACKAGED 18 PCS PER BAG
- 12 DIMENSION "C" TO BE 6.0 INCHES MIN
- 13 PITCH: FIVE (5) LOUVERS PER INCH (NOMINAL)
- 14 LENGTH 5.438 INCHES REF 28 LOUVERS
- 15.FINISH - SILVER PLATE 200μINCHES MIN THK.
- 16 PRELIMINARY PART NUMBER
- 17 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 18 LENGTH 12.0 INCHES
REFERENCE 62 LOUVERS
- 19 SPECIAL PACKAGING

OBSOLETE	19	C	25.91 [1.02]	18	1-2	15	0.15 [.008]	--	2-192000-3
		C	25.91 [1.02]	14	17-2	15	0.25 [.010]	--	2-192000-2
	1211 OBSOLETE 17	A	25.02 [.98]	10	UNPLATED	45	0.25 [.010]	--	2-192000-1
		A	25.02 [.98]	9	UNPLATED	45	0.25 [.010]	--	2-192000-0
		A	25.02 [.98]	8	1-2	45	0.25 [.010]	--	1-192000-9
		A	25.02 [.98]	8	UNPLATED	45	0.25 [.010]	--	1-192000-8
		A	25.02 [.98]	5	1-2	45	0.25 [.010]	--	1-192000-7
		A	25.02 [.98]	4	1-2	45	0.25 [.010]	--	1-192000-6
		A	25.02 [.98]	5	UNPLATED	45	0.25 [.010]	--	1-192000-5
		A	25.02 [.98]	4	UNPLATED	45	0.25 [.010]	--	1-192000-4
OBSOLETE									1-192000-3
									1-192000-2
									1-192000-1
17	OBSOLETE	C	25.02 [.98]	7	1-2	45	0.25 [.010]	00009	1-192000-1
	OBSOLETE	C	25.02 [.98]	7	UNPLATED	45	0.25 [.010]	00012	1-192000-0
	OBSOLETE	C	25.91 [1.02]	7	1-2	15	0.25 [.010]	00006	192000-9
17	OBSOLETE	C	25.91 [1.02]	7	UNPLATED	15	0.25 [.010]	00015	192000-8
	OBSOLETE								192000-7
	OBSOLETE								192000-6
	OBSOLETE	C	25.02 [.98]	7	1-2	45	0.15 [.006]	00018	192000-5
17	OBSOLETE	C	25.02 [.98]	7	UNPLATED	45	0.15 [.006]	00017	192000-4
		C	25.91 [1.02]	7	3-2	15	0.15 [.006]	00021	192000-3
		C	25.91 [1.02]	7	1-2	15	0.15 [.006]	00002	192000-2
	OBSOLETE	C	25.91 [1.02]	7	UNPLATED	15	0.15 [.006]	00001	192000-1
	STYLE	WIDTH A	NUMBER OF LOUVER	PLATING (NOTE NO)	TOOTH ANGLE	MAT'L THK	HUGIN PN	PART NUMBER	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[192000-2](#)