

REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
	V	REVISED PER ECO-15-011608	04NOV2015	NK	MZ
	W	REVISED PER ECO-18-000435	17JAN2018	RS	MZ
	Y	REVISED PER ECO-19-014914	27SEP2019	RS	MZ

The image contains two technical drawings of louvers.
STYLE A (FEMALE): This drawing shows a cross-section of a female louver. It has a curved, ribbed profile. Dimensions include a width of 8.1 with a tolerance of [.32] and a circular end view labeled '(FREE DIA)'.
STYLE C (STRIP): This drawing shows a cross-section of a strip louver. It has a flat, ribbed profile. Dimensions include a length labeled 'LENGTH MIN', a width of 8.1 with a tolerance of [.32], and a height labeled '(LOUVER HEIGHT)'. A side view shows the louver's profile with a label 'LH' for louver height.

- 1 FINISH—SILVER PLATE 200 μINCH THICK MIN.
2 FINISH—NICKEL PLATE 40 μINCH THICK MIN.
3 FINISH—GOLD PLATE 10 μINCH THICK MIN.
4 FINISH
5 FINISH—GOLD PLATE 40 μINCH THICK MIN.
6 FINISH—TIN PLATE 300 μINCH THICK MIN.
7 FINISH—GOLD PLATE 50 μINCH THICK MIN.
8 FINISH—NICKEL PLATE 100 μINCH THICK MIN.
9 FINISH—PREPLATE
10
11 PLATING NOTES ARE TO BE INTERPRETED AS FOLLOWS,
6—8 AS 6 OVER 8.
12 MATERIAL—CDA172, BeCu.
13 MATERIAL—STAINLESS STEEL
14 PRODUCT IS SOLD BY THE FOOT.

15 OBSOLETE (PENDING).

16 MATERIAL: ELGILOY.

17 PRELIMINARY PART NUMBER.


18 FINISH: COPPER PLATE 10 uINCH THICK MIN.

19 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09-21-91 RA JAYNE		 TE Connectivity									
		CHK 07-21-93 J.TURNER											
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONTACT BAND, FEMALE									
		APVD —											
		PRODUCT SPEC —											
		APPLICATION SPEC —											
0 PLC ± — 1 PLC ± — 2 PLC ± 0.5 [.02] 3 PLC ± 0.25 [.010] 4 PLC ± — ANGLES ± —		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL —		FINISH SEE TABLE		WEIGHT —		A2		00779		C-192043		—	
CUSTOMER DRAWING						SCALE 1:1		SHEET 1 of 2		REV Y			

THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				ALL RIGHTS RESERVED.					
© COPYRIGHT - By -													
A	[.09]	[.024]	--	12	1.57	[.062]	3-2	7	0.12	[.005]	--	9-192043-9	OBSOLETE
A	[.21]	[.026]	--	12	4.39	[.173]	3-18	17	0.15	[.006]	--	9-192043-8	
A	[.17]	[.026]	--	16	3.17	[.125]	3-2	13	0.12	[.005]	--	9-192043-7	
A	[1.00]	[.026]	--	12	18.4	[.725]	1-2	73	0.15	[.006]	--	9-192043-6	
C	--	[.038]	NOTE	14	12	--	1-2	9	0.15	[.006]	--	9-192043-5	OBSOLETE
A	[.16]	[.026]	--	12	3.2	[.125]	3-2	11	0.15	[.006]	--	9-192043-4	OBSOLETE
A	[.21]	[.026]	--	12	3.98	[.157]	1-2	14	0.15	[.006]	--	9-192043-3	
A	[.21]	[.026]	--	12	3.98	[.157]	UNPL	14	0.15	[.006]	--	9-192043-2	
C	--	[.016]	NOTE	14	12	--	UNPL	--	0.12	[.005]	--	9-192043-1	
C	--	[.030]	NOTE	14	12	--	UNPL	--	0.15	[.006]	--	9-192043-0	OBSOLETE
A	[.58]	[.024]	--	12	11.1	[.439]	UNPL	44	0.20	[.008]	--	8-192043-9	OBSOLETE
A	[.50]	[.024]	--	12	10.4	[.410]	UNPL	40	0.20	[.008]	--	8-192043-8	
--	--	--	--	--	--	--	--	--	--	--	--	8-192043-7	
A	[.40]	[.024]	--	12	10.4	[.408]	1-2	40	0.15	[.006]	04220	8-192043-6	
A	[.29]	[.024]	--	12	6.3	[.250]	UNPL	26	0.20	[.008]	--	8-192043-5	OBSOLETE
A	[.26]	[.024]	--	12	5.5	[.217]	UNPL	21	0.15	[.006]	--	8-192043-4	
C	--	[.026]	NOTE	14	12	--	UNPL	--	0.15	[.006]	--	8-192043-3	
A	[.19]	[.024]	--	12	4.7	[.187]	UNPL	18	0.15	[.006]	--	8-192043-2	
C	--	[.030]	[.46]	--	12	--	UNPL	15	0.15	[.006]	--	8-192043-1	OBSOLETE
A	[.17]	[.028]	--	12	3.2	[.125]	7-2	13	0.15	[.006]	--	8-192043-0	
A	[.65]	[.024]	--	12	15.3	[.602]	UNPL	60	0.15	[.006]	04224	7-192043-9	
C	--	[.036]	NOTE	14	12	-	1-2	-	0.15	[.006]	--	7-192043-8	
A	[.16]	[.026]	--	12	3.17	[.125]	UNPL	11	0.15	[.006]	04229	7-192043-7	OBSOLETE
A	[.21]	[.024]	--	12	3.98	[.157]	1-2	15	0.15	[.006]	04230	7-192043-6	OBSOLETE
A	[.06]	[.018]	--	12	.6	[.025]	UNPL	4	0.12	[.005]	04225	7-192043-5	
A	[.16]	[.026]	--	12	3.2	[.125]	8	11	0.15	[.006]	04227	7-192043-4	
C	--	[.026]	NOTE	14	12	--	1-2	--	0.12	[.005]	04001	7-192043-3	
A	[.16]	[.026]	--	12	3.2	[.125]	1-2	11	0.15	[.006]	04228	7-192043-2	OBSOLETE
C	[.16]	[.036]	.37	12	--	--	UNPL	12	0.15	[.006]	04221	7-192043-1	
--	--	--	--	--	--	--	--	--	--	--	--	7-192043-0	
A	--	--	--	12	25.4	[1.00]	7-2	--	0.20	[.008]	04058	6-192043-9	
A	--	--	--	12	18	[.709]	7-2	--	0.20	[.008]	04056	6-192043-8	OBSOLETE
A	[.65]	[.024]	--	12	15.3	[.602]	7-2	60	0.15	[.006]	04074	6-192043-7	OBSOLETE
A	--	[.024]	--	12	12	[.472]	8	48	0.20	[.008]	04172	6-192043-6	OBSOLETE
A	[.72]	[.024]	--	12	12	[.472]	3-2	48	0.20	[.008]	04090	6-192043-5	OBSOLETE
A	[.72]	[.024]	--	12	12	[.472]	1-2	48	0.20	[.008]	04095	6-192043-4	
A	[.72]	[.024]	--	12	12	[.472]	UNPL	48	0.20	[.008]	04096	6-192043-3	
A	--	--	--	12	12	[.472]	3-2	48	0.15	[.006]	04055	6-192043-2	
A	--	--	--	12	12	[.472]	1-2	48	0.15	[.006]	04091	6-192043-1	OBSOLETE
A	[.58]	[.024]	--	12	11.1	[.439]	3-2	44	0.20	[.008]	04205	6-192043-0	OBSOLETE
A	[.58]	[.024]	--	12	11.1	[.439]	1-2	44	0.20	[.008]	04201	5-192043-9	OBSOLETE
A	[.57]	[.024]	--	12	10.4	[.410]	3-2	40	0.20	[.008]	04154	5-192043-8	
A	[.50]	[.024]	--	12	10.4	[.408]	3-2	40	0.15	[.006]	04186	5-192043-7	
A	[.50]	[.024]	--	12	10.4	[.408]	UNPL	40	0.15	[.006]	04187	5-192043-6	
A	[.50]	[.024]	--	12	9.5	[.375]	1-2	38	0.20	[.008]	04115	5-192043-5	
A	[.50]	[.024]	--	12	9.5	[.375]	UNPL	38	0.20	[.008]	04176	5-193043-4	
A	[.45]	[.030]	--	12	9.5	[.375]	3-2	38	0.18	[.007]	04209	5-192043-3	
A	[.45]	[.030]	--	12	9.5	[.375]	6	38	0.18	[.007]	04207	5-192043-2	
A	[.45]	[.030]	--	12	9.5	[.375]	UNPL	38	0.18	[.007]	04208	5-192043-1	
STYLE	(FREE DIA)	LH	LENGTH	MAT'L (NOTE)	MATING PIN Ø REF	PLATING (NOTE NO.)	NUM LOUV	MAT'L THK	REF	PART NUMBER			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RA JAYNE 09-21-91	TE Connectivity		
		CHK J.TURNER 07-21-93			
DIMENSIONS: mm[INCHES]		APVD -	NAME		
		PRODUCT SPEC	CONTACT BAND, FEMALE		
		APPLICATION SPEC			
		SIZE CAGE CODE DRAWING NO			
		RESTRICTED TO			
MATERIAL -	FINISH SEE TABLE	WEIGHT -	A200779C-192043		
CUSTOMER DRAWING			SCALE 1:1	SHEET 2 OF 2	REV Y

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-192043-0](#)