





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	00	E		REVISED PER ECO-13-010626	07AUG2013	KH
		F		REVISED PER ECO-19-009248	05JUL2019	AP



- 1 MATERIAL:
CONTACT - PHOS BRONZE
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- 2 FINISH:
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
- 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE AND STANDARD IN APPROXIMATE AREA SHOWN
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
5. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 6 REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- 7 SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIMATE AREA.



○ = SIGNAL
⊗ = GROUND
RECOMMENDED PC BOARD
LAYOUT BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. MAGARO 08JUN2007	TE Connectivity	
DIMENSIONS:		CHK W. DAVIS 08JUN2007		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W. DAVIS 08JUN2007	NAME	
	0 PLC ±	PRODUCT SPEC	HEADER ASSEMBLY, RIGHT WALL, 3 PAIR, 10 COLUMN TinMan	
	1 PLC ±	APPLICATION SPEC		
MATERIAL	2 PLC ±	WEIGHT	SIZE	RESTRICTED TO
- 1	3 PLC ±	-	A100779C=1934341	-
	4 PLC ±	Customer Drawing	SCALE 8:1	SHEET 1 OF 1
	ANGLES			REV F
	FINISH			
	- 2			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1934341-1](#)