





THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
ALL RIGHTS RESERVED.
© COPYRIGHT - BY -

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A				RELEASED PER ECO 13-008999	5-29-13	CT	KH



MATING FACE



△ FRONT & REAR INSULATOR: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.
CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194
REAR GROMMET: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1

△ DATE CODE: YEAR & WEEK (YY WW)

△ THE PART NUMBER MAY BE MARKED EITHER ON THE REAR INSULATOR OR GROMMET.

4. DESCRIPTIVE PART NUMBER: GPRBEP3SA
THIS INSERT CONTAINS 3 CAVITIES FOR GPR SIZE 5 SOCKET CONTACTS, 1954722-1.

5. THIS PRODUCT IS SOLD BY TE CONNECTIVITY UNDER A LICENSE FROM RADIALL SA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		0 PLC	±-
0 PLC	±-	1 PLC	±-
1 PLC	±-	2 PLC	±-
2 PLC	±-	3 PLC	±-
3 PLC	±-	4 PLC	±-
4 PLC	±-	ANGLES	±-
MATERIAL		FINISH	

DWN
BH

CHK
JPM

APVD
JPM

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

5JAN07

5JAN07

5JAN07

5JAN07

5JAN07

5JAN07

5JAN07



TE Connectivity

NAME: INSERT ASSEMBLY, SOCKET, FOR POWER
CONTACTS, ENVIRONMENTAL,
ARRANGEMENT P3, KEY A, GPRB

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A200779	C-1954327		-

SCALE 4:1 SHEET 1 OF 1 REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1954327-1](#)