


4

3

2


1

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			A	REL PER ECR 08-001116	15JAN08	JR MS



- 1 STAMP AMP, LOCATE APPROX AS SHOWN.
- 2 WIRE INSULATION DIA .050-.082.
- 3 TONGUE MATL THK .018±.002
- 4 MATERIAL:
BODY - COPPER PER ASTM B-152
SLEEVE - COPPER PER ASTM B-152
- 5 FINISH:
BODY, TIN-LEAD 60/40, .000300 MIN THK
SLEEVE, TIN-LEAD 60/40, .000300 MIN THK
- 6 MAXIMUM RECOMMENDED OPERATING TEMP
170°C MAX
- 7 CIRCULAR MIL AREA:
0.10mm-0.41mm2 [202-810], STRANDED WIRE

1000	LOOSE PIECE	1958074-1
QTY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth	15JAN07	 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL, RING, DIAMOND GRIP, WIRE SIZE 26-22 AWG —	
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .008 4 PLC ± — ANGLES ± 5°			
MATERIAL 	FINISH 	CHK M SPICER	15JAN07	SIZE A3	CAGE CODE 00779
		APVD M SPICER		DRAWING NO C-1958074	
		PRODUCT SPEC —		RESTRICTED TO —	
		APPLICATION SPEC —		CUSTOMER DRAWING	
		WEIGHT —		SCALE 8:1	SHEET 1 OF 1
				REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1958074-1](#)