


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECR-15-016687	10CT15	L.P	T.D
	A2	REVISED PER ECR-16-014132	05OCT2016	MD	MD

D

C

B

A







- 1 TO ENSURE PROPER MATING OF RECEPTACLE TO TAB, TAB LENGTH ON PLUNGER SWITCH SHOULD BE A MINIMUM OF 8.25 [.325].
- 2 MATERIAL IS UL94 V0 AND 150°C RATED.
- 3 ACCEPTS .187 SERIES BUDGET FASTON STRAIGHT RECEPTACLES SUCH AS P/N 63477-X
- 4 ACCEPTS .110 SERIES POSITIVE-LOCK MARK III STRAIGHT RECEPTACLES FOR .032" THK TAB, P/N 1742975-1.

D

C

B

A



SCALE 4:1

1969725-1

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	11FEB15	TE Connectivity			
DIMENSIONS: mm[INCHES]		CHK	DAVE HUMPHREY	11FEB15				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	DAVE HUMPHREY	11FEB15	NAME HOUSING, RECEPTACLE, 187 FASTON, WITH .110 POSI-LOCK, DOOR SWITCH			
0 PLC ±		PRODUCT SPEC	-	-				
1 PLC ±		APPLICATION SPEC	-	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2 PLC ±0.25 [.010]		WEIGHT	-	-	A2	00779	C-1969725	-
3 PLC ±		CUSTOMER DRAWING		SCALE	5:1	SHEET	1 OF 1	REV
4 PLC ±								A2
ANGLES ±								
FINISH								
MATERIAL								
6/6 NYLON								
COLOR-BLACK								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1969725-1](#)