






P	LTR	DESCRIPTION	DATE	DWN	APVD
A6		ECR-15-016520	25NOV2015	SL	RR
A7		ECR-17-001536	03FEB2017	IZ	RR
A8		ECR-18-008584	05JUN2018	BW	LZ
A9		ECR-18-009485	19MAY2019	BW	WW


NOTE

- 1 SEE SHEET 2 FOR AVAILABLE CONFIGURATIONS
- 2 MATERIAL: HOUSING, NYLON, UL94 V0, 750°C GWT NO FLAME
EIGHT COLORS AVAILABLE, INCLUDING: NATURAL,
RED, BLUE, YELLOW, BLACK, GREY, GREEN, PURPLE
WHITE VERSION IS PRELIMINARY
- CONTACT, COPPER ALLOY, 0.60MM THICK
- 3 FINISH: OPTION 1: TIN PLATING OVER NICKEL UNDERPLATING
OPTION 2: AG PLATING OVER NICKEL UNDERPLATING
- 4 PCB LAYOUT AS SHOWN
- 5 THE PART NUMBERS SHOWING IN SHEET 2 & 3
ARE FOR NATURAL COLOR . THE PART NUMBER FOR OTHER COLOR
ARE BASED ON THE NATURAL ONE: FOR THE SAME CONFIGURATION,
THE PREFIX AND POSTFIX OF THE P/N ARE THE SAME, ONLY THE
BASE NUMBER IS DIFFERENT ACCORDING TO DIFFERENT COLOR,
DETAIL PLEASE SEE SHEET 4
- 6 PACKAGING: LOOSE PIECE OR TUBE. THE PART NUMBERS IN THIS
DRAWING ARE WITH LOOSE PIECE PACKAGING. PLEASE CONTACT TE
SALES REPRESENTATIVES FOR TUBE PACKAGING REQUIREMENT.
- 7 PRELIMINARY PART NOT RELEASED FOR PRODUCTION



PCB LAYOUT - SOLDER SIDE
SCALE 4:1

N	M	NO. OF POS.
40.10	35.00	8 LOAD,15 POS.
35.10	30.00	7 LOAD,13 POS.
30.10	25.00	6 LOAD,11 POS.
25.10	20.00	5 LOAD,9 POS.
20.10	15.00	4 LOAD,7 POS.
15.10	10.00	3 LOAD,5 POS.
10.10	5.00	2 LOAD,3 POS.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WINTER WANG	12NOV2012	STE TE Connectivity	
		CHK HAPYE WU	12NOV2012		
DIMENSIONS: mm		APVD YUHHONG MAO	12NOV2012	NAME RAST 2.5 TAB HEADER ASSY, SELECTIVE LOADED, TH, VERTICAL, EXTERNAL LOCKING	
		PRODUCT SPEC 108-106079			
		APPLICATION SPEC -		SIZE A2	CAGE CODE 00779
MATERIAL -		WEIGHT -		DRAWING NO C-1971921	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE NTS	SHEET 1	OF 5
				REV A9	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

ES

00

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

8

7

6

5

4

3

2

QTY

TAB CONTACT

w/ SILVER PLATING

QTY

HOUSING

5

POS.

TE PART NO.

5

15

13

11

9

7

5

3

3

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 15P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 13P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 11P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 9P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 7P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 5P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 3P
(SEE THE DETAIL LAYOUT ON SHEET 3)

3-1971924-5

2-1971924-5

1-1971924-5

1-1971924-3

2-1971924-1

1-1971924-1

6-1971923-9

5-1971923-9

4-1971923-9

3-1971923-9

2-1971923-9

1-1971923-9

8-1971923-7

7-1971923-7

6-1971923-7

5-1971923-7

4-1971923-7

3-1971923-7

2-1971923-7

1-1971923-7

6-1971923-5

5-1971923-5

4-1971923-5

3-1971923-5

2-1971923-5

1-1971923-5

1971923-3

9-1971923-3

8-1971923-3

7-1971923-3

6-1971923-3

5-1971923-3

4-1971923-3

3-1971923-3

2-1971923-3

1-1971923-3

8

7

6

5

4

3

2

QTY

TAB CONTACT

w/ TIN PLATING

QTY

HOUSING

5

POS.

TE PART NO.

5

15

13

11

9

7

5

3

3

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 15P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 13P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 11P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 9P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 7P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 5P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 3P
(SEE THE DETAIL LAYOUT ON SHEET 3)

3-1971922-5

2-1971922-5

1-1971922-5

1-1971922-3

2-1971922-1

1-1971922-1

6-1971921-9

5-1971921-9

4-1971921-9

3-1971921-9

2-1971921-9

1-1971921-9

8-1971921-7

7-1971921-7

6-1971921-7

5-1971921-7

4-1971921-7

3-1971921-7

2-1971921-7

1-1971921-7

9-1971921-5

8-1971921-5

7-1971921-5

6-1971921-5

5-1971921-5

4-1971921-5

3-1971921-5

2-1971921-5

1-1971921-5

1971921-3

9-1971921-3

8-1971921-3

7-1971921-3

6-1971921-3

5-1971921-3

4-1971921-3

3-1971921-3

2-1971921-3

1-1971921-3

8

7

6

5

4

3

2

QTY

TAB CONTACT

w/ TIN PLATING

QTY

HOUSING

5

POS.

TE PART NO.

5

15

13

11

9

7

5

3

3

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 15P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 13P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 11P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 9P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 7P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 5P
(SEE THE DETAIL LAYOUT ON SHEET 3)

RAST 2.5 TAB HEADER HOUSING,
EXTERNAL LOCKING, 3P
(SEE THE DETAIL LAYOUT ON SHEET 3)

3-1971922-5

2-1971922-5

1-1971922-5

1-1971922-3

2-1971922-1

1-1971922-1

6-1971921-9

5-1971921-9

4-1971921-9

3-1971921-9

2-1971921-9

1-1971921-9

8-1971921-7

7-1971921-7

6-1971921-7

5-1971921-7

4-1971921-7

3-1971921-7

2-1971921-7

1-1971921-7

9-1971921-5

8-1971921-5

7-1971921-5

6-1971921-5

5-1971921-5

4-1971921-5

3-1971921-5

2-1971921-5

1-1971921-5

1971921-3

9-1971921-3

8-1971921-3

7-1971921-3

6-1971921-3

5-1971921-3

4-1971921-3

3-1971921-3

2-1971921-3

1-1971921-3

1471-9 (3/11)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
BOB YANG

CHK
HAPYE WU

APVD
YUHHONG MAO


PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

DIMENSIONS:
mm



0 PLC ±
1 PLC ±
2 PLC ±0.20
3 PLC ±
4 PLC ±
ANGLES ±°
FINISH

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±°

29MAY2012

12NOV2012

12NOV2012

12NOV2012

NAME
RAST 2.5 TAB HEADER ASSY,
SELECTIVE LOADED, TH, VERTICAL,
EXTERNAL LOCKING

SIZE
A2

CAGE CODE
00779

DRAWING NO
1971921

RESTRICTED TO
-

SCALE
NTS

SHEET
2

OF
5

REV
A9

TE Connectivity

301

1-1971921-3

1-1971923-3

5

301

5-1971921-3

5-1971923-3

5

301

2-1971921-3

2-1971923-3

5

301

6-1971921-3

6-1971923-3

5

301

3-1971921-3

3-1971923-3

5

301

7-1971921-3

7-1971923-3

5

301

4-1971921-3

4-1971923-3

5

301

8-1971921-3

8-1971923-3

5

301

9-1971921-3

9-1971921-3

5

301

1971921-3

1971921-3

5

3_POS

50301

1-1971921-5

1-1971923-5

5

50301

8-1971921-5

8-1971923-5

5

50301

2-1971921-5

2-1971923-5

5

50301

9-1971921-5

9-1971923-5

5

50301

3-1971921-5

3-1971923-5

5

50301

6-1971921-5

6-1971923-5

5

50301

4-1971921-5

4-1971923-5

5

50301

7-1971921-5

7-1971921-5

5

50301

5-1971921-5

5-1971923-5

5

5_POS

7050301

1-1971921-7

1-1971923-7

5

7050301

5-1971921-7

5-1971923-7

5

7050301

2-1971921-7

2-1971923-7

5

7050301

6-1971921-7

6-1971923-7

5

7050301

3-1971921-7

3-1971923-7

5

7050301

7-1971921-7

7-1971923-7

5

7050301

4-1971921-7

4-1971923-7

5

7050301

8-1971921-7

8-1971923-7

5

7_POS

907050301

1-1971921-9

1-1971923-9

5

907050301

2-1971921-9

2-1971923-9

5

907050301

5-1971921-9

5-1971923-9

5

907050301

3-1971921-9

3-1971923-9

5

907050301

6-1971921-9

6-1971923-9

5

907050301

4-1971921-9

4-1971923-9

5

9_POS

110907050301

1-1971922-1

1-1971924-1

5

130110907050301

1-1971922-3

1-1971924-3

5

150130110907050301

1-1971922-5

1-1971924-5

5

150130110907050301

2-1971922-5

2-1971924-5

5

150130110907050301

3-1971922-5

3-1971924-5

5

15_POS

301

NO CONTACT LOADED

KEYING GROOVE

PICTORIAL VIEW KEY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN BOB YANG 12NOV2012

CHK HAPYE WU 12NOV2012

APVD YUHONG MAO 12NOV2012

NAME

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±0.20

3 PLC ±

4 PLC ±

ANGLES ±°

FINISH

RAST 2.5 TAB HEADER ASSY
SELECTIVE LOADED, TH, VERTICAL,
EXTERNAL LOCKING

SIZE A1

CAGE CODE 00779

DRAWING NO C=1971921

RESTRICTED TO

SCALE NTS

SHEET 3 OF 5

REV A9

4805 13/111

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.
BY -

RELEASED FOR PUBLICATION
ALL RIGHTS RESERVED.

LOC
-

DIST
-

P	LFR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

50001

1-2825332-5

5_POS

600001

1-2825332-6

6_POS

7650301

1-2825332-7

7_POS

00650321

1-2825332-8

8_POS

907604021

1-2825332-9

9_POS

0987650301

1-2825332-0

10_POS

604021

2-2825332-6

650301

3-2825332-6

87604301

2-2825332-8

980604301

2-2825332-9

△

PRELIMINARY PART - NOT RELEASED FOR PRODUCTION
PART NUMBERS X-2825332-X ARE EQUIVALENT TO #-1971921-# IN GEOMETRY AND MATERIAL,
WITH ADDITIONAL POSITIONS, CONTACT LOADING AND POLARIZATIONS, AS SHOWN.

NO CONTACT LOADED

KEYING GROOVE

PICTORIAL VIEW KEY

301

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.20
3 PLC ±
4 PLC ±
ANGLES ±°
FINISH

MATERIAL
-

FINISH
-

DWN
BOB YANG
CHK
HAPYE WU
APVD
YUHONG MAO

12NOV2012
12NOV2012
12NOV2012

NAME
YUHONG MAO

PRODUCT SPEC
APPLICATION SPEC

WEIGHT
-

CUSTOMER DRAWING

STE

TE Connectivity

RAST 2.5 TAB HEADER ASSY
SELECTIVE LOADED, TH, VERTICAL,
EXTERNAL LOCKING

SIZE
A1

CAGE CODE
00779

DRAWING NO
C=1971921

RESTRICTED TO
-

SCALE
NTS

SHEET
4

OF
5

REV
A9

4805 13/111

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC-

DIST-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

FOR ANY KEYING CONFIGURATION, THERE ARE EIGHT COLORS AVAILABLE, BESIDES THE NATURAL COLOR, THERE ARE OTHER SEVEN COLORS, INCLUDE: YELLOW, BLUE, GREY, PURPLE, RED, GREEN, BLACK. THE WHITE VERSION IS PRELIMINARY. THE P/N OF THE COLOR CONNECTOR ARE BASED ON THE NATURAL CONNECTOR, THE PREFIX AND POSTFIX ARE THE SAME FOR THE SAME KEYING CONFIGURATION, BUT THE BASE NUMBERS ARE DIFFERENT ACCORDING TO DIFFERENT COLOR.THE FOLLOWING SHOWS WHAT’S THE P/N FOR COLOR CONNECTOR

#-1971921-#

PREFIX

BASE NUMBER

POSTFIX

COLOR	PART NUMBER OF THE CONNECTOR 5				COMMENTS
	WITH TIN PLATING CONTACT		WITH AG PLATING CONTACT		
NATURAL	#-1971921-#	#-1971922-#	#-1971923-#	#-1971924-#	THE DETAIL P/N FOR DIFFERENT KEYING SEE SHEET 2 & 3
RED	#-2232189-#	#-2232190-#	#-2232191-#	#-2232192-#	THE PREFIX AND POSTFIX ARE THE SAME WITH THE P/N OF THE NATURAL CONNECTOR FOR THE SAME KEYING CONFIGURATION, JUST THE BASE NUMBERS ARE DIFFERENT BASED ON DIFFERENT COLOR. # CAN BE THE NUMBER FROM 0 TO 9.
BLUE	#-1971984-#	#-1971985-#	#-2232193-#	#-2232194-#	
YELLOW	#-2232195-#	#-2232196-#	#-2232197-#	#-2232198-#	
BALCK	#-2232199-#	#-2232200-#	#-2232201-#	#-2232202-#	
GREY	#-2232203-#	#-2232204-#	#-2232205-#	#-2232206-#	
GREEN	#-2232207-#	#-2232208-#	#-2232209-#	#-2232210-#	
PURPLE	#-2232211-#	#-2232212-#	#-2232213-#	#-2232214-#	
WHITE	#-2232285-#	#-2232286-#	#-2232287-#	#-2232288-#	

FOR EXAMPLE,IF A CONNECTOR WITH THE CONFIGURATION AS BELOW, AND WITH TIN PLATING CONTACT, IN THE SHEET 4, WE CAN FIND THE RELATED CONNECTOR P/N WITH NATURAL COLOR IS 3-1971921-3, THEN WE CAN LOOK IN THE ABOVE TABLE TO FIND THE CONNECTOR P/N WITH RED COLOR IS 3-2232189-3

301

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±0.2

3 PLC ±

4 PLC ±

ANGLES ±°

FINISH

MATERIAL

-

DWN 12NOV2012 WINTER WANG

CHK 12NOV2012 HAPYE WU

APVD 12NOV2012 YUHONG MAO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

Customer Drawing

TE Connectivity

NAME RAST 2.5 TAB HEADER ASSY
SELECTIVE LOADED, TH, VERTICAL,
EXTERNAL LOCKING

SIZE A2

CAGE CODE 00779

DRAWING NO C-1971921

RESTRICTED TO

SCALE 5:1

SHEET 5 OF 5

REV A9

1471-9 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-1971921-3](#)