

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .


© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	CUTTING BURR DETAILS ADDED	19NOV2018	RK	PS

1. MATERIAL:
HOUSING: POLYAMIDE 6 UL94V-0.
COLOR: BROWN.
TUBULAR CONTACT: BRASS, TIN PLATED.
SCREW: M5, STEEL, ZINC PLATED W/ NON-HEXAVALENT CHROMATE (CHROME III).
WIRE PROTECTOR: STAINLESS STEEL
2. ELECTRICAL:
CURRENT RATING: 65A, 600V.
WIRE RANGE: 6-14 UL AND 6-22 AWG FOR (CSA)
3. CONTINUOUS WORKING TEMP.: 150°C MAX.
4. CUTTING PROJECTION CAN BE ON BOTH SIDES
DEPENDING ON CUTTING LOCATION.
5. CUTTING BURR MAX. 1mm ALLOWED.



145.0	170.7	TSB2000K12DSHT	1-1986469-2
130.5	156.2	TSB2000K11DSHT	1-1986469-1
116.0	141.7	TSB2000K10DSHT	1-1986469-0
101.5	127.2	TSB2000K09DSHT	1986469-9
87.0	112.7	TSB2000K08DSHT	1986469-8
72.5	98.2	TSB2000K07DSHT	1986469-7
58.0	83.7	TSB2000K06DSHT	1986469-6
43.5	69.2	TSB2000K05DSHT	1986469-5
29.0	54.7	TSB2000K04DSHT	1986469-4
14.5	40.2	TSB2000K03DSHT	1986469-3
-	25.7	TSB2000K02DSHT	1986469-2
-	11.2	TSB2000K01DSHT	1986469-1
DIM B	DIM A	CATALOG NUMBER	TE PART NUMBER

1986469-4 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 9/17/08	 TE Connectivity Ltd.				
		CHK C RICHARD 9/17/08					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC± − 1 PLC± 0.3 2 PLC± 0.25 3 PLC± − 4 PLC± − ANGLES± 2°	APVD C RICHARD 9/17/08	NAME 14.5MM PITCH WIRE PROTECTOR 65A HIGH VOLTAGE VERSION, HIGH TEMP —				
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL SEE NOTES		FINISH SEE NOTES	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C=1986469	RESTRICTED TO —
CUSTOMER DRAWING					SCALE NTS	SHEET 1 OF 1	REV A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1986469-0](#)