


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
FT	0		A2	REVISED PER ECO-11-005027		11MAR11	HMR

MATERIALS:
HOUSING: PA66, UL94V-0, COLOR: GREEN.
CONTACT: PHOS BRONZE, TIN PLATED.
WIRE GUARD: STEEL, ZINC CHROMATE.
CAGE CLAMP: STEEL, ZINC CHROMATE.
SCREW: STEEL, ZINC PLATED.


ELECTRICAL:
VOLTAGE RATING: 300V.
CURRENT RATING: 16A.
INSULATION RESISTANCE 2000Mohm/DC500V.
WITHSTANDING VOLTAGE AC2000V MIN
WIRE RANGE: 14-24 AWG

MECHANICAL:
SCREW TORQUE: 7.0 IN-LB
WIRE STRIP LENGTH: 10mm




ENVIRONMENTAL:
WORKING TEMP.: -40°C TO +105°C.



2-1986484-5



2-1986484-6



SEE DETAIL	1	121.92±0.5	24	2-1986484-4
	1	116.84±0.5	23	2-1986484-3
	1	111.76±0.5	22	2-1986484-2
	1	106.68±0.5	21	2-1986484-1
	1	101.60±0.5	20	2-1986484-0
	1	96.52±0.5	19	1-1986484-9
	2	91.44±0.5	18	2-1986484-6
	1	91.44±0.5	18	1-1986484-8
	1	86.36±0.5	17	1-1986484-7
	1	81.28±0.5	16	1-1986484-6
	1	76.20±0.5	15	1-1986484-5
	1	71.12±0.5	14	1-1986484-4
	1	66.04±0.5	13	1-1986484-3
		60.96±0.5	12	1-1986484-2
		55.88±0.5	11	1-1986484-1
		50.80±0.5	10	1-1986484-0
		45.72±0.5	9	1986484-9
		40.64±0.5	8	1986484-8
		35.56±0.5	7	1986484-7
		30.48±0.5	6	1986484-6
SEE DETAIL	2	25.40±0.5	5	2-1986484-5
	1	25.40±0.5	5	1986484-5
		20.32±0.5	4	1986484-4
		15.24±0.5	3	1986484-3
		10.16±0.5	2	1986484-2
		DIM L	NO OF POS	PART NUMBER

- 1 PRELIMINARY PART NUMBER
- 2 PART MARKED WITH BLACK PERMANENT MARKING

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.2

2 PLC ± 0.10

3 PLC ± -

4 PLC ± -

ANGLES ± 1°

MATERIAL -

FINISH -

DWN S SCHLEGEL 17NOV2008

CHK C RICHARD 11/17/08

APVD C RICHARD 11/17/08

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

TE Connectivity

NAME

TERMINAL BLOCK, PLUG, 5.08mm PITCH

SIZE A3

CAGE CODE 00779

DRAWING NO C-1986484

RESTRICTED TO -

CUSTOMER DRAWING

SCALE NTS

SHEET 1 OF 1

REV A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1986484-7](#)