


LOC		DIST		REVISIONS								
-		-		P		LTR		DESCRIPTION		DATE	DWN	APVD
						A		RELEASED PER ECO-11-000354		12JAN2011	RL	RPW
						B		REV. PER ECO-11-011392		09JUN2011	RJM3	DM



STRAIN RELIEF CLAMP HALVES  
2 REQD  
MAT'L: THERMOPLASTIC  
COLOR: BLACK  
PACKAGED UNASSEMBLED

WIRE TIES  
SHOWN FOR REFERENCE ONLY  
CUSTOMER SUPPLIED

CABLE  
SHOWN FOR REFERENCE ONLY



CONNECTOR SHELL  
SHOWN FOR REFERENCE ONLY



SCREW, #2-56 CAPTIVE  
4 REQD  
MAT'L: STAINLESS STEEL  
(SCREWS ARE PRE-ASSEMBLED)

AS SHOWN	2000739-1
REMARKS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	D. FABIAN	11FEB2008			
		CHK	-	-			
		APVD	-	-			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME	
IN		9 PLC ±.01		APPLICATION SPEC		KIT, STRAIN RELIEF	
		3 PLC ±.01				LOW PROFILE RETANGULAR QUADRA	
		5 PLC ±.005				404, SIZE 3	
		4 PLC ±.0005					
		ANGLES ±.1					
MATERIAL		FINISH		WEIGHT		RESTRICTED TO	
SEE CALL-OUT		SEE CALL-OUT		-		-	
				CUSTOMER DRAWING			
				SCALE		SHEET	
				4:1		1 OF 1	
						REV	
						B	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2000739-1](#)