


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	8						
			AC2	REVISED PER ECO-11-004917	11MAR11	RK	HMR

D

C

B


A



MARKING
SEE TABLE

MATING FACE

C'BORE OPTIONAL
ACROSS FLATS
2 PLC



RECOMMENDED PANEL CUTOUT

- 1. PHENOLIC PER MIL-M-14, TYPE CFG, BLACK.
- 2. DIALLYL PHTHALATE PER MIL-M-14, TYPE SDG-F, BLUE.
- 3. AMP PART NO THIS AREA. DATE CODE AT AMP'S OPTION.
- 4. MARK KS 21303, L10.
- 5. WHEN MATING WITH BLOCK 201357, ACCOMODATES TYPE II, TYPE III+ OR TYPE VI #16 PIN OR SOCKET CONTACTS.
- 6. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	Z	Y	MARKING	MATERIAL	PART NUMBER
6	43.08 [1.696]	3.86 [.152]	3 4	2	200838-9
	43.08 [1.696]	3.86 [.152]	3	2	200838-3
	42.82 [1.686]	3.99 [.157]	3	1	200838-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.REIFSNYDER 07 DEC 95	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R.STONE 29 FEB 96				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G.A.STEINHAUER 20 MAR 96	BLOCK, FEMALE, 34 PLACE MINIATURE RECTANGULAR, M SERIES			
0 PLC ± -		PRODUCT SPEC				
1 PLC ± -		APPLICATION SPEC				
2 PLC ± 0.13 [.005]		WEIGHT -				
3 PLC ± -		CUSTOMER DRAWING				
4 PLC ± -		SCALE 3:1				
ANGLES ± 1°		SHEET 1 OF 1				
FINISH -		REV AC2				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[200838-2](#)