

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.


REVISIONS

変更




P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECR-17-017423	29NOV2017	T.S	E.I

22POS(X-KEY)
: 2-2013325-1
2-2069573-1
2-2069574-1

△2△3
CONTACT TAB



RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1



10	35.0	42.3	44.3	X	22	YELLOW	2-2069574-1
						NATURAL	2-2069573-1
						BLACK	2-2013325-1
5	17.5	24.8	26.8	X	12	YELLOW	1-2069574-6
						NATURAL	1-2069573-6
						BLACK	1-2013325-6
3	10.5	17.8	20.2	X	8	YELLOW	1-2069574-4
						BLACK	1-2013325-4
n	A	B	C	KEY	POS.	COLOR	PART NO

△1.MATERIAL:HOUSING:66 NYLON GLASS FILLED(UL94V-0)
CONTACT:COPPER ALLOY
RETENTION LEG:PRE-TIN COPPER ALLOY

△2.FINISH(ALL OVER):NICKEL PLATING 1.27μmMIN

△3.FINISH(CONTACT AREA):GOLD PLATING 0.38μmMIN AFTER △2

△4.FINISH(CONTACT TAIL):TIN PLATING 2μmMIN AFTER △2
5.THE SHAPE, SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE.
THEY DON'T SHOW DETAILS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±5° 0-PLC ± 1-PLC ±0.5 2-PLC ±0.13 3-PLC ±0.013 4-PLC ±0.0001 ANGLES ± FINISH 仕上
MATERIAL 材料	△1
	△2△3△4

DWN	M. MAEBASHI	09MAY2008
CHK	T. KUDO	09MAY2008
APVD	S. MANABE	09MAY2008
PRODUCT SPEC	108-78336	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING		

TE

TE Connectivity

NAME
名称 DYNAMIC D1900D 3.5mmPITCH
HDR ASSY (V-TYPE)
-

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C-2013325	-
SCALE 尺度	4:1	SHEET 1 OF 2	REV D1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20


© COPYRIGHT 20

BY -


ALL RIGHTS RESERVED.

REVISIONS





P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



12POS(X-KEY) : I-2013325-6
I-2069573-6
I-2069574-6



8POS(X-KEY) : I-2013325-4
I-2069574-4



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.5
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±0.0001
ANGLES ±
FINISH

DWN 09MAY2008

M. MAEBASHI

CHK 09MAY2008

T. KUDO

APVD 09MAY2008

S. MANABE

PRODUCT SPEC

108-78336

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME
DYNAMIC D1900D 3.5mmPITCH
HDR ASSY (V-TYPE)

-

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2013325

-

SCALE

4:1

SHEET

2 OF 2

REV

D1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2013325-6](#)