

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.





© COPYRIGHT - By -

| LOC | DIST | REVISIONS | | | | |
|-----|------|-----------|-----|---------------------------|---------|-----|
| | | P | LTR | DESCRIPTION | DATE | DWN |
| CM | 00 | | | | | |
| | | C1 | | REVISED PER ECO-11-005027 | 11MAR11 | RK |
| | | D | | REVISED PERECR-14-015945 | 26OCT14 | A.Z |

POSITION 1
IDENTIFICATION
FEATURE







- 1 MATERIAL: HOUSING: NYLON 66 GF20, UL94V-0, NATURAL
CONTACTS: BRASS, TIN-PLATED
- 2 GLOW WIRE APPROVED, CONTACT TE CONNECTIVITY
ENGINEERING FOR SPECIFICATION.



PCB LAYOUT: COMPONENT SIDE
RECOMMENDED BOARD THICKNESS 1.78 [.070]

| | | | | |
|-----|---------------------|--------------|--------------|-------------|
| 24 | 46.2±0.2 [1.82±.01] | 51.60 [2.03] | 55.60 [2.19] | 2-2029059-4 |
| 22 | 42.0±0.2 [1.65±.01] | 47.40 [1.87] | 51.40 [2.02] | 2-2029059-2 |
| 20 | 37.8±0.2 [1.49±.01] | 43.20 [1.70] | 47.20 [1.86] | 2-2029059-0 |
| 18 | 33.6±0.2 [1.32±.01] | 39.00 [1.54] | 43.00 [1.69] | 1-2029059-8 |
| 16 | 29.4±0.2 [1.16±.01] | 34.80 [1.37] | 38.80 [1.53] | 1-2029059-6 |
| 14 | 25.2±0.2 [.99±.01] | 30.60 [1.21] | 34.60 [1.36] | 1-2029059-4 |
| 12 | 21.0±0.2 [.83±.01] | 26.40 [1.04] | 30.40 [1.20] | 1-2029059-2 |
| 10 | 16.8±0.1 [.66±.00] | 22.20 [.87] | 26.20 [1.03] | 1-2029059-0 |
| 8 | 12.6±0.1 [.50±.00] | 18.00 [.71] | 22.00 [.87] | 2029059-8 |
| 6 | 8.4±0.1 [.33±.00] | 13.80 [.54] | 17.80 [.70] | 2029059-6 |
| 4 | 4.2±0.1 [.17±.00] | 9.60 [.38] | 13.60 [.54] | 2029059-4 |
| 2 | | 5.40 [.21] | 9.40 [.37] | 2029059-2 |
| POS | A | B±0.2 [.01] | C±0.35 [.01] | PART NUMBER |

2-2029059-4 SHOWN

| | | | | | | | |
|---|--|--|---|--|---|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | | DWN K. WHITAKER 15JAN2008 | |  TE Connectivity | | |
| DIMENSIONS: mm [INCHES] | | | CHK C. CASH 15JAN2008 | | | | |
|  | | | APVD C. CASH 15JAN2008 | | NAME VERTICAL HEADER WITH PEGS, WITH DRAIN HOLES VAL-U-LOK(TM) | | |
| | | | PRODUCT SPEC 108-2112 | | | | |
| | | | APPLICATION SPEC 114-13172 | | | | |
| | | | SIZE A2 | | | | |
| MATERIAL  | | | FINISH  | | CAGE CODE 00779 | | |
| | | | | | DRAWING NO C-2029059 | | |
| | | | | | RESTRICTED TO — | | |
| | | | CUSTOMER DRAWING | | SCALE N/A | | |
| | | | | | SHEET 1 of 1 | | |
| | | | | | REV D | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2029059-0](#)