



PART AFTER
UNRESTRICTED RECOVERY

TABLE OF DIMENSIONS:

PART NUMBER	H		J			P	R	S	T	JO	HW	JW	U
	Min a	Max b	POLY Min a	VITON Min a	Max b	±10% b	±15% b	±10% b	±20% b	±10% b	±20% b	±20% b	±20% b
202D211-X-32	.88 (22,3)	.45 (11,5)	.88 (22,3)	.55 (13,9)	.25 (6,4)	3.00 (76,2)	.46 (11,7)	.12 (3,05)	.040 (1,02)	2.23 (56,6)	.06 (1,52)	.045 (1,14)	.55 (14,0)
202D221-X-32	1.01 (25,6)	.59 (15,0)	1.01 (25,6)	.63 (16,0)	.29 (7,4)	3.25 (82,6)	.48 (12,2)	.12 (3,05)	.040 (1,02)	2.36 (59,9)	.06 (1,52)	.045 (1,14)	.59 (15,0)
202D232-X-32	1.16 (29,4)	.74 (18,8)	1.16 (29,4)	.72 (18,2)	.33 (8,4)	3.50 (88,9)	.48 (12,2)	.12 (3,05)	.040 (1,02)	2.48 (63,0)	.07 (1,78)	.045 (1,14)	.60 (15,2)
202D242-X-32	1.34 (34,0)	.90 (22,9)	1.34 (34,0)	.84 (21,3)	.38 (9,7)	4.00 (101,6)	.48 (12,2)	.12 (3,05)	.040 (1,02)	2.87 (72,9)	.07 (1,78)	.045 (1,14)	.62 (15,7)
202D253-X-32	1.47 (37,3)	1.16 (29,5)	1.47 (37,3)	.91 (23,1)	.41 (10,5)	4.25 (108,0)	.55 (14,0)	.12 (3,05)	.065 (1,65)	2.85 (72,4)	.08 (2,03)	.045 (1,14)	.70 (17,8)
202D263-X-32	1.72 (43,6)	1.34 (34,1)	1.72 (43,6)	1.07 (27,1)	.48 (12,2)	4.50 (114,3)	.60 (15,2)	.12 (3,05)	.065 (1,65)	2.92 (74,2)	.08 (2,03)	.045 (1,14)	.78 (19,8)
202D274-X-32	1.97 (50,0)	1.62 (41,2)	1.97 (50,0)	1.24 (31,4)	.56 (14,3)	4.65 (118,1)	.60 (15,2)	.12 (3,05)	.065 (1,65)	2.86 (72,6)	.09 (2,29)	.055 (1,40)	.78 (19,8)
202D285-X-32	2.47 (62,7)	1.85 (47,0)	2.47 (62,7)	1.54 (39,1)	.69 (17,6)	4.75 (120,7)	.63 (16,0)	.12 (3,05)	.08 (2,03)	2.78 (70,6)	.10 (2,54)	.055 (1,40)	.81 (21,0)
202D296-X-32	2.73 (69,3)	2.35 (59,7)	2.73 (69,3)	1.70 (43,1)	.77 (19,6)	5.00 (127,0)	.63 (16,0)	.12 (3,05)	.08 (2,03)	2.64 (67,1)	.10 (2,54)	.055 (1,40)	.81 (21,0)
202D299-X-32	3.22 (81,7)	2.64 (67,1)	3.22 (81,7)	2.01 (51,0)	.90 (22,9)	5.25 (133,4)	.63 (16,0)	.12 (3,05)	.08 (2,03)	2.70 (68,6)	.10 (2,54)	.055 (1,40)	.81 (21,0)

NOTES:

1. All dimensions are in inches (millimeters)
2. Dimensions appearing in Table are as follows:
a - As supplied
b - After unrestricted recovery
3. Part shall have injection and vent ports, located as shown.

ORDERING INFORMATION:

Base part number 202D221 -4 -32
Material dash number _____
-3 Polyolefin, semi-rigid (RT-301/7)
-4 Polyolefin, flexible (RT-1304)
-12 Viton (RT-1312)
-25 Elastomer, fluid-resistant (RT-1325)
Modification number _____

SPECIFICATION CONTROL DRAWING (LIMITED DISTRIBUTION)

If this document is printed it becomes uncontrolled.
Check for the latest revision.

THIS DRAWING AND THE INFORMATION SET FORTH HEREON ARE THE PROPERTY OF RAYCHEM CORPORATION, AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE, OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY RAYCHEM CORPORATION IS PROHIBITED.

DO NOT SCALE THIS DRAWING

DRAWN	R. W. W. 10-8-80	Raychem		RAYCHEM CORPORATION 300 CONSTITUTION DRIVE MENDOTA PARK, CALIFORNIA 93604	
CHECKED	W. H. W. 10/10/80			TITLE	
DESIGN APPD	W. H. W. 10/10/80	BOOT, STRAIGHT, WITH LIP			
MFG APPD	W. H. W. 10/10/80				
QC APPD	W. H. W. 10/10/80				
MKTG APPD	W. H. W. 10/10/80				
Trace Service	R. W. W. 10/10/80	CODE IDENT.	DRWG. NO.	202D2XX-X-32	
		NO. 00000			
PROJECT		SIZE 8	SCALE	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[132094-000](#) [186065N001](#) [202798N001](#) [208067-000](#) [246499N001](#) [309527-000](#) [808502N001](#) [503061-000](#) [115989-000](#) [299359-000](#) [160493-000](#) [CS3165-000](#) [003942-000](#) [A91731-000](#) [808391N006](#) [EG1913-000](#) [CN8460-000](#) [CC3910-000](#) [CY0332-000](#) [606096-000](#) [530952-000](#) [040571-000](#) [057151-000](#) [097331-000](#) [811303-005](#) [811210N005](#) [400769N001](#) [837893-000](#) [CM4233-000](#) [D89023-000](#) [033809N002](#) [037750-000](#) [988671N002](#) [996795-000](#) [CB7008-000](#) [CL8041-000](#) [CL8042-000](#) [CM3294-000](#) [526575N001](#) [551209-000](#) [617279-000](#) [897623-000](#) [913281-000](#) [918255N001](#) [807592-000](#) [808011-000](#) [444773-000](#) [481529-000](#) [481667-000](#) [482859N002](#) [814635N003](#) [776993-000](#) [792219N001](#) [806531-000](#) [806542N001](#) [806910-000](#) [324647-000](#) [811236-000](#) [811241-000](#) [811584-000](#) [814526N002](#) [814587N002](#) [202D263-4-32-0](#) [202D253-12-32-0](#) [202D232-12-32-0-CS5463](#)