

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

NOV ,2008.

© COPYRIGHT 2008 By -

ALL RIGHTS RESERVED.

LOC
JDIST
/

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD


E

REVISED ECR-12-012475


9JUL2012

Y.K


A.K

リール引出し方向
DIRECTION OFF TOP OF REEL



VIEW W

テープ幅 32mm以上に適用
APPLIED TAPE WIDTH 32MM,MORE.

VIEW W

テープ幅 12mm, 16mm, 24mmに適用
APPLIED TAPE WIDTH 12MM, 16MM AND 24MM.

DETAIL X



50 POCKETS

空部 400mm 程度
WITHOUT CHARGE APPROX

W

WINDING THE COVER TAPE
ARROUND THE OUTER
PERIPHERY IN A TURN.
カバーテープ・リーダー部剥離角度
165°~180°
PEELING
ANGLE

30 POCKETS MIN

空部 240mm MIN
WITHOUT CHARGE MIN

△ GENERAL TOLERANCE
10 ≥ : ±0.2
30 ≥ >10: ±0.25
100 ≥ >30: ±0.3
ANGLES: ±3°

△ DIM. 28.4 AND DETAIL "X" APPLIED
TAPE WIDE, 32mm MORE.

△ 一般公差
10以下: ±0.2
10を越え 30以下: ±0.25
30を越え 100以下: ±0.3
角 度: ±3°

△ 28.4寸法及び "X" 詳細図は、
テープ幅 32mm以上に適用

OBSOLETE	AVAILABLE	0.115g	30.4	24.4	17.2	24	—	11.5	3500	61	2-2040832-6
	AVAILABLE	0.098g	30.4	24.4	14.7	24	—	11.5	3500	51	2-2040832-1
	AVAILABLE	0.087g	30.4	24.4	13.2	24	—	11.5	3500	45	1-2040832-8
	AVAILABLE	0.080g	30.4	24.4	12.2	24	—	11.5	3500	41	1-2040832-6
	AVAILABLE	0.074g	30.4	24.4	11.2	24	—	11.5	3500	37	1-2040832-4
OBSOLETE	AVAILABLE	0.053g	22.4	16.4	8.2	16	—	7.5	3500	25	2040832-8
STATUS		CONNECTOR WEIGHT	F	E	D	C	B	A	数量(ヶ)	POS.(N)	EMBOSS TAPE PACKAGING PART NUMBER
			DIMENSIONS						QTY/REEL		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN Y.KODAIRA 17NOV2008

CHK A.KUBO 26NOV2008

APVD T.KUSUHARA 26NOV2008

PRODUCT SPEC

製品規格

108-78650

APPLICATION SPEC

取付適用規格

411-78338

WEIGHT

NAME 名称

0.25FPC BF-L-1.3H

1.3mmH, 3.2mmW, GOLD PLATE

SIZE CAGE CODE DRAWING NO 番号

A3 00779 C-2040832

RESTRICTED TO

CUSTOMER DRAWING

SCALE 尺度 NTS

SHEET 1 OF 2

REV E

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

NOV , 2008.

© COPYRIGHT 2008 By -

ALL RIGHTS RESERVED.

LOC
JDIST
/

REVISIONS

変更

P

LTR





DESCRIPTION

DATE

DWN





APVD

SEE SHEET 1



RECOMMENDED PCB PATTERN DIMENSION

15.5	14.5	15.0	16.0	17.0	61	2-2040832-6
13.0	12.0	12.5	13.5	14.5	51	2-2040832-1
11.5	10.5	11.0	12.0	13.0	45	1-2040832-8
10.5	9.5	10.0	11.0	12.0	41	1-2040832-6
9.5	8.5	9.0	10.0	11.0	37	1-2040832-4
6.5	5.5	6.0	7.0	8.0	25	2040832-8
L	K	J	H	G	POS.	CONN. PART NO

Z-Z (20:1)
(ACTUATOR OPEN CONDITION)Z-Z (20:1)
(ACTUATOR CLOSE CONDITION)RECOMMENDED FPC PATTERN DIMENSION
CONDUCTOR : GOLD OVER NICKEL PLATING (Au 0.1μm MIN.)

3. MATERIAL
HOUSING : GRASS FULLED LCP, UL94V-0 (COLOR : NATURAL)
ACTUATOR : GRASS FULLED PPS, UL94V-0 (COLOR : BLACK)
FRONT CONTACT : COPPER ALLOY
REAR CONTACT : COPPER ALLOY
SOLDER PEG : COPPER ALLOY

4. FINISH
FRONT CONTACT : GOLD OVER NICKEL PLATING
REAR CONTACT : GOLD OVER NICKEL PLATING
SOLDER PEG : TIN OVER NICKEL PLATING

5. THIS PRODUCT IS THE NICKEL DAM TYPE.

- △ THE SUPPORTING TAPE OF FPC IS RECOMMENDED
TO USE THE POLYIMIDE OR THE EQUIVALENT MATERIAL
OF THE THICKNESS OF 50μm OR MORE.


3. 材質
ハウジング：ガラス繊維入りLCP樹脂 UL94V-0（色：乳白色）
アクチュエーター：ガラス繊維入りPPS樹脂 UL94V-0（色：黒）
フロントコンタクト：銅合金
リアコンタクト：銅合金
ソルダーペグ：銅合金

4. めっき
フロントコンタクト：金めっき（ニッケル下地めっき）
リアコンタクト：金めっき（ニッケル下地めっき）
ソルダーペグ：スズめっき（ニッケル下地めっき）

5. 本品は、Ni ダム仕様のコネクタである。

- △ FPC の補強板には、厚さ50μm 以上のポリイミドまたは相当材
の使用を推奨する。

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位： 耗
mmMATERIAL
材料TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH
仕上

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

STE

TE Connectivity

NAME
名称

0.25FPC BF-L-1.3H
1.3mmH, 3.2mmW, GOLD PLATE

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

A300779

C-2040832

SCALE
尺度 NTS

SHEET

2 OF 2

REV
E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2040832-4](#)