

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

NOV ,2008.

© COPYRIGHT 2008 By -

ALL RIGHTS RESERVED.

LOC
JDIST
/

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD


E

REVISED ECR-12-012475


9JUL2012

Y.K


A.K

リール引出し方向
DIRECTION OFF TOP OF REEL



VIEW W

テープ幅 32mm以上に適用
APPLIED TAPE WIDTH 32MM,MORE.

VIEW W

テープ幅 12mm, 16mm, 24mmに適用
APPLIED TAPE WIDTH 12MM, 16MM AND 24MM.

DETAIL X

リール径
REEL DIAMETER
Ø330 REF

50 POCKETS

空部 400mm 程度
WITHOUT CHARGE APPROX製品装填部
WITH PRODUCT CHARGE

30 POCKETS MIN

空部 240mm MIN
WITHOUT CHARGE MINWINDING THE COVER TAPE
ARROUND THE OUTER
PERIPHERY IN A TURN.
カバーテープ・リーダー部外周一巻き
165°~180°
PEELING
ANGLE△ GENERAL TOLERANCE
10 ≥: ±0.2
30 ≥ >10: ±0.25
100 ≥ >30: ±0.3
ANGLES: ±3°△ DIM. 28.4 AND DETAIL "X" APPLIED
TAPE WIDE, 32mm MORE.△ 一般公差
10以下: ±0.2
10を越え 30以下: ±0.25
30を越え 100以下: ±0.3
角 度: ±3°△ 28.4寸法及び "X" 詳細図は、
テープ幅 32mm以上に適用

OBSOLETE	AVAILABLE	0.115g	30.4	24.4	17.2	24	—	11.5	3500	61	2-2040832-6
	AVAILABLE	0.098g	30.4	24.4	14.7	24	—	11.5	3500	51	2-2040832-1
	AVAILABLE	0.087g	30.4	24.4	13.2	24	—	11.5	3500	45	1-2040832-8
	AVAILABLE	0.080g	30.4	24.4	12.2	24	—	11.5	3500	41	1-2040832-6
	AVAILABLE	0.074g	30.4	24.4	11.2	24	—	11.5	3500	37	1-2040832-4
OBSOLETE	AVAILABLE	0.053g	22.4	16.4	8.2	16	—	7.5	3500	25	2040832-8
STATUS		CONNECTOR WEIGHT	F	E	D	C	B	A	数量(ヶ)	POS.(N)	EMBOSS TAPE PACKAGING PART NUMBER
			DIMENSIONS						QTY/REEL		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN Y.KODAIRA 17NOV2008

CHK A.KUBO 26NOV2008

APVD T.KUSUHARA 26NOV2008

PRODUCT SPEC

製品規格

108-78650

APPLICATION SPEC

取付適用規格

411-78338

WEIGHT

NAME

名称

STE

TE Connectivity

0.25FPC BF-L-1.3H

1.3mmH, 3.2mmW, GOLD PLATE

SIZE

CAGE CODE

DRAWING NO

番号

A3

00779

C=

2040832

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE

尺度 NTS

SHEET

1 OF 2

REV

E

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

NOV , 2008.

© COPYRIGHT 2008 By -

ALL RIGHTS RESERVED.

LOC
JDIST
/

REVISIONS

変更

P

LTR





DESCRIPTION

DATE

DWN





APVD

SEE SHEET 1



RECOMMENDED PCB PATTERN DIMENSION

15.5	14.5	15.0	16.0	17.0	61	2-2040832-6
13.0	12.0	12.5	13.5	14.5	51	2-2040832-1
11.5	10.5	11.0	12.0	13.0	45	1-2040832-8
10.5	9.5	10.0	11.0	12.0	41	1-2040832-6
9.5	8.5	9.0	10.0	11.0	37	1-2040832-4
6.5	5.5	6.0	7.0	8.0	25	2040832-8
L	K	J	H	G	POS.	CONN. PART NO

Z-Z (20:1)
(ACTUATOR OPEN CONDITION)Z-Z (20:1)
(ACTUATOR CLOSE CONDITION)RECOMMENDED FPC PATTERN DIMENSION
CONDUCTOR : GOLD OVER NICKEL PLATING (Au 0.1μm MIN.)

3. MATERIAL

HOUSING : GRASS FULLED LCP, UL94V-0 (COLOR : NATURAL)
 ACTUATOR : GRASS FULLED PPS, UL94V-0 (COLOR : BLACK)
 FRONT CONTACT : COPPER ALLOY
 REAR CONTACT : COPPER ALLOY
 SOLDER PEG : COPPER ALLOY

4. FINISH

FRONT CONTACT : GOLD OVER NICKEL PLATING
 REAR CONTACT : GOLD OVER NICKEL PLATING
 SOLDER PEG : TIN OVER NICKEL PLATING

5. THIS PRODUCT IS THE NICKEL DAM TYPE.

△ THE SUPPORTING TAPE OF FPC IS RECOMMENDED
 TO USE THE POLYIMIDE OR THE EQUIVALENT MATERIAL
 OF THE THICKNESS OF 50μm OR MORE.

3. 材質

ハウジング：ガラス繊維入りLCP樹脂 UL94V-0（色：乳白色）
 アクチュエーター：ガラス繊維入りPPS樹脂 UL94V-0（色：黒）
 フロントコンタクト：銅合金
 リアコンタクト：銅合金
 ソルダーペグ：銅合金

4. めっき

フロントコンタクト：金めっき（ニッケル下地めっき）
 リアコンタクト：金めっき（ニッケル下地めっき）
 ソルダーペグ：スズめっき（ニッケル下地めっき）

5. 本品は、Ni ダム仕様のコネクタである。

△ FPC の補強板には、厚さ50μm 以上のポリイミドまたは相当材
 の使用を推奨する。

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

STE

TE Connectivity

NAME
名称

0.25FPC BF-L-1.3H
 1.3mmH, 3.2mmW, GOLD PLATE

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

A300779

C-2040832

SCALE
尺度 NTS

SHEET

2 OF 2

REV
E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2040832-8](#)