








P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED (ECR-19-011814)	26JUL2019	HX	WH



NOTE:


1. MATERIAL:  
HOUSING: LCP, WITH 40% GF, UL 94V-0, NATURAL COLOR.  
SPACER: LCP, WITH 30% GF, UL 94V-0, BLACK COLOR.  
CONTACTS: PHOSPHOR BRONZE.  
HOLD DOWN: BRASS.
2. FINISH:  
CONTACTS: GOLD FLASH PLATED ALL CONTACT AREA,  
1.27 $\mu$ m [50 $\mu$ "] MIN. NICKEL UNDERPLATED OVER ALL.  
HOLD DOWN: 3.04 $\mu$ m [120 $\mu$ "]~5.08 $\mu$ m [200 $\mu$ "] MATTE-TIN OVER ALL.  
1.27 $\mu$ m [50 $\mu$ "] MIN. NICKEL UNDERPLATED OVER ALL.
3. REFLOW SOLDER CAPABLE TO 260°C PER TEST SPEC.  
109-201, CONDITION B.




RECOMMENDED P.C. BOARD PATTERN LAYOUT  
METAL MASK: T=0.15, TOLERANCE:  $\pm 0.05$

POS.	PN	DIM.A	DIM.B	DIM.C	DIM.D	DIM.E	DIM.F	DIM.G	DIM.H	DIM.I
40	4-2041215-0	19.50	24.90	20.60	20.65	25.23	22.00	25.60	22.10	20.50
60	2041215-1	29.50	34.90	30.60	30.65	35.23	32.00	35.60	32.10	30.50

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
		0 PLC	± -
		1 PLC	± 0.30
		2 PLC	± 0.20
		3 PLC	± 0.15
		4 PLC	± -
		ANGLES	± -
MATERIAL		FINISH	
SEE NOTE		SEE NOTE	

DWN J. LAI	17SEP2009	 TE Connectivity			
CHK S. CHIEN	17SET2009				
APVD W. KODAMA	NAME  ZIF FPC 0.50mm PITCH CONNECTOR, 2.5mm HIGH, LOCK TYPE				
PRODUCT SPEC 108-57789					
APPLICATION SPEC —					
WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-2041215	RESTRICTED TO —	
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 OF 1	REV C







THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

TE Connectivity Ltd.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



10800	6	1800	4-2041215-0
9000	5	1800	2041215-1
QUANTITY(PCS)	REEL/CARTON	PCS/REEL	PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LAI 17SEP2009	TE Connectivity		
		CHK S. CHIEN 17SET2009			
DIMENSIONS: mm		APVD W. KODAMA	NAME		
		PRODUCT SPEC 108-57789	ZIF FPC 0.50mm PITCH CONNECTOR, 2.5mm HIGH, LOCK TYPE		
		APPLICATION SPEC —			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C=2041215
MATERIAL SEE NOTE		FINISH SEE NOTE	RESTRICTED TO —		
CUSTOMER DRAWING			SCALE 1:1	SHEET 2 of 2	REV C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2041215-1](#)