












LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L	REVISED PER ECO-14-011808	09AUG2014	AP	SB





4"AMP", PART NO. & DATE CODE, MARKED
IN AREA INDICATED, ON FAR SIDE

- 1 CONNECTOR ACCEPTS SIZE 20 DF PIN CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
- 2 CONNECTOR COMPLIES WITH 108-40005 WHERE APPLICABLE.
- 3 MOLDED PARTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK
- 4 SHELLS: STEEL PER ASTM A109.
- 5 ZINC PLATED PER ASTM B633; TYPE II; CLASS SC1; YELLOW CHROMATE
- 6 TIN OR TIN-LEAD PLATED OVER COPPER UNDERPLATE.
- 7 CHROME PLATED.
- 8 TIN PLATED OVER COPPER UNDERPLATE.
- 9 ZINC PLATED .000200-.000400 THICK, YELLOW TRIVALENT CHROMIUM CHROMATE COATING.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



A10	OBSOLETE	SMALL PACK		NO	1-205204-0-
		STANDARD		NO	205204-9
		STANDARD		NO	205204-8
	SUPERSEDED BY 205204-9	SMALL PACK		NO	205204-7
		STANDARD		YES	205204-4
	SUPERSEDED BY 205204-8	STANDARD		NO	205204-3
	OBSOLETE	STANDARD		NO	205204-2
	SUPERSEDED BY 205204-9	STANDARD		NO	205204-1
		PACKAGING TYPE	SHELL FINISH	GROUNDING INDENTS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 07/19/85		 TE Connectivity	
		CHK J. GERACE 07/29/85			
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		NAME PLUG CONNECTOR, SIZE 1, 9 POS., AMPLIMITE HDP —	
MATERIAL SEE NOTES		FINISH SHELLS: SEE TABLE		SIZE A2	CAGE CODE 00779
		WEIGHT —		DRAWING NO C-205204	RESTRICTED TO —
CUSTOMER DRAWING				SCALE NTS	SHEET 1 of 1
				REV 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[205204-9](#)