




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00						
			L	REVISED PER ECO-14-011808	09AUG2014	AP	SB



- CONNECTOR ACCEPTS SIZE 20 DF PIN CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
- CONNECTOR COMPLIES WITH 108-40005 WHERE APPLICABLE.
- GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK
- STEEL PER ASTM A109.
- ZINC PLATED PER ASTM B633; TYPE II; CLASS SC1; YELLOW CHROMATE.
- TIN OR TIN-LEAD PLATED OVER COPPER UNDERPLATE.
- TIN PLATED OVER COPPER UNDERPLATE.
- ZINC PLATED .000200-.000400 THICK, YELLOW TRIVALENT CHROMIUM CHROMATE COATING.



OBSOLETE	STANDARD	8	NO	205206-9
	STANDARD	7	NO	205206-8
	SMALL PACK	5	NO	205206-6
OBSOLETE	STANDARD	7	YES	205206-3
OBSOLETE	STANDARD	6	NO	205206-2
OBSOLETE	STANDARD	5	NO	205206-1
PACKAGING TYPE		SHELL FINISH	GROUNDING INDENTS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	7-19-85	TE Connectivity			
DIMENSIONS: INCHES		CHK	7-29-85				
		APVD	7-31-85	NAME			
		PRODUCT SPEC					
		APPLICATION SPEC		PLUG CONNECTOR, SIZE 2, 15 POSITION, AMPLIMITE HDP			
MATERIAL MOLDED PARTS: 3		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SHELLS: 4		FINISH		A2	00779	C=205206	-
		SHELLS: SEE TABLE		CUSTOMER DRAWING			
				SCALE	NTS	SHEET	1 OF 1
						REV	L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[205206-9](#)