




1. CONNECTOR ACCEPTS SIZE 20 DF SOCKET CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.

2. CONNECTOR COMPLIES WITH 108-40005 WHERE APPLICABLE.

3 GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK

4 STEEL PER ASTM A109.

5 ZINC PLATED PER ASTM B633; TYPE II; CLASS SC1; YELLOW CHROMATE.

6 TIN OR TIN-LEAD PLATED PER MIL-T-10727.

7 TIN PLATED PER MIL-T-10727 OVER COPPER PER MIL-C-14550.

8 ZINC PLATED .000200-.000400 THICK, YELLOW TRIVALENT CHROMIUM CHROMATE COATING.

SUPERSEDED BY 205209-1

OBSOLETE	STANDARD	8	.120	205209-7
	SMALL PACK	5	.120	205209-6
	STANDARD	6	.154	205209-3
	STANDARD	7	.120	205209-2
OBSOLETE	STANDARD	5	.120	205209-1
	PACKAGING TYPE	SHELL FINISH	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
INCHES	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± .005
	4 PLC ± -
	ANGLES ± -

MATERIAL	FINISH	WEIGHT	SCALE	SHEET	REV
SEE NOTES	SHELLS: SEE TABLE	-	4:1	1 OF 1	L

DWN S.WELDON	7-19-85	TE Connectivity		
CHK J.GERACE	7-29-85			
APVD -	-			
PRODUCT SPEC -	-			
APPLICATION SPEC -	-	NAME RECEPTACLE CONNECTOR, SIZE 4, 37 POSITION, AMPLIMITE HDP		
CUSTOMER DRAWING	SIZE A2	CAGE CODE 00779	DRAWING NO C=205209	RESTRICTED TO -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[205209-7](#)