


P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	REVISED PER ECO-14-011808	09AUG2014	AP	SB



1. CONNECTOR ACCEPTS SIZE 20 DF SOCKET CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.

2. CONNECTOR COMPLIES WITH 108-40005 WHERE APPLICABLE.

3 GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK

4 STEEL PER ASTM A109.

5 ZINC PLATED PER ASTM B633; TYPE II; CLASS SC1; YELLOW CHROMATE.

6 TIN OR TIN-LEAD PLATED PER MIL-T-10727.

7 TIN PLATED PER MIL-T-10727 OVER COPPER PER MIL-C-14550.

8 ZINC PLATED .000200-.000400 THICK, YELLOW TRIVALENT CHROMIUM CHROMATE COATING.

SUPERSEDED BY 205209-1

OBSOLETE	STANDARD	8	.120	205209-7
	SMALL PACK	5	.120	205209-6
	STANDARD	6	.154	205209-3
	STANDARD	7	.120	205209-2
OBSOLETE	STANDARD	5	.120	205209-1
	PACKAGING TYPE	SHELL FINISH	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

MATERIAL SEE NOTES

FINISH SHELLS: SEE TABLE

DWN S.WELDON 7-19-85

CHK J.GERACE 7-29-85

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

RECEPTACLE CONNECTOR, SIZE 4, 37 POSITION, AMPLIMITE HDP

SIZE A2

CAGE CODE 00779

DRAWING NO C=205209

RESTRICTED TO -

SCALE 4:1

SHEET 1 OF 1

REV L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[205209-2](#)