




1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308

2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .068 DIA

3. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS

4. PACKAGE STAMPED M24308/2-292F

5. THIS RCPT. WILL ACCEPT SIZE 20 SOCKET CONTACT M24308/10 OR AMP # 205090

△ AMP PART NO. STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS

△ UL/CSA DESIGNATION STAMPED IN THIS AREA.

OBSOLETE	BRASS	205416-2
	STEEL PER ASTM-A-109	205416-1
	SHELL MAT'L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C.C.THOMAS
CHK
FC BALLEW III
APVD
—
PRODUCT SPEC
—
APPLICATION SPEC
—
WEIGHT
—
CUSTOMER DRAWING

12-9-87
12-10-87
—
—
—
—
—

NAME
AMPLIMITE RCPT FOR SOCKET CONTACTS
HI-DENSITY HDM-20 CONNECTOR SIZE 1 (9 POS)
SERIES 109 WITH FLOAT BUSHINGS

SIZE
A2
CAGE CODE
00779
DRAWING NO
C-205416
RESTRICTED TO
—

SCALE
4:1
SHEET
1 of 1
REV
N

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[205416-1](#)