





1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
 2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .068 DIA
 3. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS
 4. PACKAGE STAMPED M24308/2-295F
 5. THIS RCPT. WILL ACCEPT SIZE 20 SOCKET CONTACT M24308/10 OR AMP # 205090
- △ AMP PART NO. STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- △ UL/CSA DESIGNATION STAMPED IN THIS AREA, OPTIONAL

OBSOLETE	BRASS	205419-2
	STEEL PER ASTM-A-109	205419-1
	SHELL MAT'L	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± .005 3 PLC DEC ± .005 ANGLES ± 0°30'	DR 12-9-87 C.C. THOMAS	AMP AMP INCORPORATED Harrisburg, Pa. 17105 NAME AMPLIMITE RCPT. FOR SOCKET CONTACTS HI-DENSITY "HDM-20" CONNECTOR SIZE 4 (37 POSN) SERIES 109 WITH FLOAT BUSHINGS
	CHK 12-10-87 F.C. BALLEW III	
	APPD 12-10-87 F.C. BALLEW III	
	APPD 12-10-87 D.J.M.	
MATERIAL	PRODUCT SPEC	SIZE FSCH NO DRAWING NO REV D 00779 205419 M SCALE 4:1 SHEET 1 OF 1
SEE CALLOUTS	-	
FINISH	APPLICATION SPEC	
SEE CALLOUTS	-	
WEIGHT	-	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[205419-1](#)