


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVO
GP	00		AB	REVISED PER ECO-14-011808	09AUG2014	AP	SB

D


C

B


A



AMP, PART NO & DATE CODE
MARKED IN AREA INDICATED,
ON FAR SIDE



- 1. MOLDED PARTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK
SHELLS: CARBON STEEL. BLACK.
CONTACTS: BRASS.
- 2. SHELLS: 5.08µm [.000200] MIN ZINC WITH YELLOW CHROMATE COATING.
CONTACTS: GOLD PLATED FOR LENGTH OF 3.81 [.150] MIN FROM MATING END, 0.76µm [.000030] MIN GOLD IN MATED AREA, 2.54µm [.000100] MIN TIN-LEAD ON SOLDER END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
OR
GOLD FLASH OVER PALLADIUM NICKEL PLATED FOR LENGTH OF 3.81 [.150] MIN FROM MATING END, 0.76µm [.000030] MIN TOTAL IN MATED AREA, 2.54µm [.000100] MIN TIN-LEAD ON SOLDER END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 3. NOTE DELETED.
- 4. NOTE DELETED.
- 5. NOTE DELETED.
- 6. NOTE DELETED.
- 7. GOLD PLATED FOR LENGTH OF 3.81 [.150] MIN FROM MATING END, GOLD FLASH IN MATED AREA. 2.54µm [.000100] MIN TIN-LEAD ON SOLDER END, ALL OVER 1.27µm [.000050] MIN NICKEL.



SUPSD BY 205714-7	-	-	205714-8
	2	4.78 [.188]	205714-7
OBSOLETE	7	16.54 [.651]	205714-6
OBSOLETE	-	-	205714-5
SUPSD BY 205714-7	7	10.85 [.427]	205714-4
SUPSD BY 205714-7	2	10.85 [.427]	205714-3
SUPSD BY 205714-7	7	3.18 [.125]	205714-2
SUPSD BY 205714-7	2	3.18 [.125]	205714-1
CONTACT FINISH		A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.13 [.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

1

2

DWN J. POLIGNONE 01FEB07
CHK E. BRIANT 01FEB07
APVD E. BRIANT 01FEB07

PRODUCT SPEC 108-40025
APPLICATION SPEC 114-40013
WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

PLUG ASSY, SIZE 4,
37 POS, VERTICAL,
AMPLIMITE HDP

SIZE A2
CAGE CODE 00779
DRAWING NO C-205714
SCALE NTS
SHEET 1 of 1
REV AB

RESTRICTED TO -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[205714-7](#)