





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AB	REV PER ECO 20-005104	5-28-20	CT	DM



1. THIS RECEPTACLE WILL MATE WITH ANY PLUG CONNECTOR WITH THE SAME INSERT ARRANGEMENT AS DEFINED BY MS18273-2.
 2. MAXIMUM WIRE INSULATION TO BE USED WITH THIS RECEPTACLE IS .054 DIA.
 3. BE. CU. RETENTION CLIPS ARE INCLUDED IN INSERTS.
- △ CUSTOMER PART NUMBER MAY BE SPLIT BETWEEN FRONT AND REAR SHELL, SAME SIDE.
- △ UL/CSA DESIGNATION STAMPED IN THIS AREA, OPTIONAL.
- △ INSPECTION REQUIREMENTS PER R4383.
- △ CONNECTOR SUPPLIED WITH 17 CONTACTS, AMP PART NUMBER 206071-1. INSPECTION REQUIREMENTS PER R4383.
- △ CONNECTOR SUPPLIED WITH 25 CONTACTS, AMP PART NUMBER 206071-1. INSPECTION REQUIREMENTS PER R4383.
- △ THESE CONNECTORS ARE QUALIFIED TO GODDARD SPACE FLIGHT CENTER SPECIFICATIONS S-311-P-4.
- △ 10 RESTRICTED TO CAE ELECTRONICS ONLY.



AMP P/N 206071-1
GSFC P/N G-08-S1
(SUPPLIED WITH 206499-6 AND
206499-7 ONLY)

.120		570566-1	1-206499-0	1-206499-0
.154	△ 10 / △ 9	311P407-1S-B-15	206499-1	206499-9
.120	△ 10 / △ 9	311P407-1S-B-12	206499-4	206499-8
.120	△ 8	20025720P1015S	206499-7	206499-7
.120	△ 7 / △ 8	R4383 P15S	206499-6	206499-6
.120	△ 6	R4383 P15S-2	206499-5	206499-5
.120	△ 9	311P407-1S-B-12	206499-4	206499-4
.154		----	206499-3	206499-3
.120		R9259P15S	206499-2	206499-2
.154	△ 9	311P407-1S-B-15	206499-1	206499-1
Ø A	REMARKS	CUSTOMER P/N	MARKED AMP P/N	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M (ISO STANDARDS)		DWN P. YEAGER 020CT2006	TE Connectivity	
DIMENSIONS: INCHES		CHK D. MILLER 050CT06	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MILLER 050CT06	PRODUCT SPEC	
0 PLC ± .005		APPLICATION SPEC		RESTRICTED TO
1 PLC ± .005		WEIGHT 0.000000		
2 PLC ± .005		A1 00779 C=206499		SHEET 1 OF 1
3 PLC ± .005		CUSTOMER DRAWING		
4 PLC ± .005		SCALE 4:1		REV AB
ANGLES ± .005		SHEET 1 OF 1		
FINISH SEE CALLOUTS		SCALE 4:1		REV AB
MATERIAL SEE CALLOUTS		SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-206499-0](#)