





---	.120	8333648P1	1-206503-2	1-206503-2
---	.120	570566-4	1-206503-1	1-206503-1
	.120	311P407-4S-B-12	206503-4	206503-9
	.120	20025720P1062S	206503-8	206503-8
---	.154	SC81D139-044	206503-7	206503-7
	.120	R4383P62S	206503-6	206503-6
	.120	R4383P62S-2	206503-5	206503-5
	.120	311P407-4S-B-12	206503-4	206503-4
---	.154	N/A	206503-3	206503-3
---	.120	R9259P62S	206503-2	206503-2
	.154	311P407-4S-B-15	206503-1	206503-1
REMARKS	DIA A	CUSTOMER P/N ON CONNECTOR	TE P/N ON CONNECTOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN A.J.GRAFF	12-21-92	 TE Connectivity	
		OWN D.MILLER	12-21-92		
DIMENSIONS: INCHES 	TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APP'D D.MILLER	12-21-92	NAME AMPLIMITE RCPT ASSY,NON-MAGNETIC, SHELL SIZE 4.62 POSITION _____
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 1°		PRODUCT SPEC _____		
	FINISH		APPLICATION SPEC _____		
	WEIGHT _____		SIZE CAGE CODE DRAWING NO A1 00779 C-206503		
MATERIAL SEE CALLOUTS		SEE CALLOUTS		RESTRICTED TO _____ CUSTOMER DRAWING	
				SCALE 4:1 SHEET 1 of 1 REV AA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[206503-4](#)