

4		3		2		1													
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS											
© COPYRIGHT - By -		ALL RIGHTS RESERVED.		BD		0		P		LTR		DESCRIPTION		DATE		DWN		APVD	
										G3		REVISED PER ECO-11-004587		11MAR11		RK		HMR	

CLAMPING INSERT 2

(2) #5-20 SELF-TAPPING SCREWS,
SOLID OR SLOTTED SHANK.
MATERIAL: STEEL
LENGTH: .62±.05 5

1.600±.025 DIA

1.655±.030

CLAMPING AREA SHADED 2

1 PARTS PACKAGED UNASSEMBLED.

2 CABLE CLAMPING AREA ADJUSTABLE FROM .261 TO .517 SQ IN BY CHANGING CLAMPING INSERT.

3 1.125 MAXIMUM CABLE OUTSIDE DIAMETER.

4 BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 75 ONLY.

5 FINISH: ZINC NON-HEXAVALENT CHROMATE.

6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE		5	4 BULK	206512-6
OBSOLETE		5	INDIVIDUAL	206512-5
OBSOLETE		5	SMALL PACK	206512-4
OBSOLETE		5	SMALL PACK	206512-3
SUPERSEDED BY 206512-6		5	4 BULK	206512-2
SUPERSEDED BY 206512-5		5	INDIVIDUAL	206512-1
SCREW FINISH		PACKAGING		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL
THERMOPLASTIC

FINISH
-

DWN
A GRAFF
CHK
W.G.LENKER
APVD
-

4/29/91
7-23-92
-

PRODUCT SPEC
108-10024
APPLICATION SPEC
-

WEIGHT
-

TE Connectivity

CABLE CLAMP KIT, LARGE,
SHELL SIZE 23, CPC

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-206512

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
1:1

SHEET
1 OF 1

REV
G3

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[206512-5](#)