

D

C

B

A





D

C

B

A

REVISIONS						
P	LTR	DESCRIPTION			DATE	OWN
AA	REVISED	PER	ECO-16-011265		12AUG2016	NK
AB	REV	PER	ECO-18-000441		23JAN2018	RS
AC	REVISED	PER	ECO-20-002045		13FEB2020	RK
						MZ
						MZ



RECOMMENDED PC BOARD LAYOUT

- 1
- HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED
- 2
- CONTACT MATERIAL: BRASS PER ASTM B36
- 3
- 3.81um [.000150] MIN TIN-LEAD OVER 2.54um [.000100] MIN COPPER OR 1.27um [.000050] MIN NICKEL.
- 4
- 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 5
- 0.38um [.000015] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 6
- .000150 MIN TIN OVER .000100 MIN COPPER OR .000050 MIN NICKEL.
- 7
- 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

	11.79[.464]	4.60±0.64[.181±.025]	YES	7	NO	1-206763-4
	11.79[.464]	4.60±0.64[.181±.025]	YES	7	YES	1-206763-3
	11.79[.464]	4.60±0.64[.181±.025]	YES	6	NO	1-206763-2
	11.79[.464]	4.60±0.64[.181±.025]	YES	6	YES	1-206763-1
OBSOLETE	11.79[.464]	4.60±0.64[.181±.025]	NO	5	YES	206763-9
OBSOLETE	13.31[.524]	4.60±0.64[.181±.025]	YES	3	NO	206763-8
OBSOLETE	11.79[.464]	4.60±0.64[.181±.025]	YES	4	NO	206763-4
OBSOLETE	11.79[.464]	4.60±0.64[.181±.025]	YES	4	YES	206763-3
OBSOLETE	11.79[.464]	4.60±0.64[.181±.025]	YES	3	NO	206763-2
OBSOLETE	11.79[.464]	4.60±0.64[.181±.025]	YES	3	YES	206763-1
B	A	LATCHES	CONTACT FINISH	MOUNTING TABS	PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 03/11/92	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R.STONE 3-17-92	NAME			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC			
		0 PLC ± -	108-10033			
		1 PLC ± -	APPLICATION SPEC			
		2 PLC ± 0.13 [.005]	SIZE			
		3 PLC ± -	CAGE CODE			
MATERIAL		FINISH CONTACT: SEE TABLE	DRAWING NO			
			RESTRICTED TO			
			A1 00779 206763			
			CUSTOMER DRAWING			
			SCALE 4:1			
			SHEET 1 OF 1			
			REV AC			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-206763-2](#)