



| REVISIONS | | | | | |
|-----------|-----|---------------------------|-----------|-----|------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | Y | REVISED PER ECO-18-012313 | 06AUG2018 | RS | MZ |
| | Z | REVISED PER ECO-20-002045 | 13FEB2020 | RK | MZ |



- 1

HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.
- 2

CONTACT MATERIAL: BRASS PER ASTM B36.
- 3

3.81µm [.000150] MIN TIN OVER 2.54µm [.000100] MIN COPPER.
- 4

0.76µm [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5

.000150 MIN TIN OVER .000100 MIN CU, OR .000050 MIN NICKEL.
- 6

0.76µm [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.

| | | | |
|---|---|---|------------|
| OBSOLETE | 6 | NO | 1-207158-1 |
| | 6 | YES | 1-207158-0 |
| | 5 | NO | 207158-8 |
| | 5 | YES | 207158-7 |
| OBSOLETE | 4 | NO | 207158-4 |
| | 4 | YES | 207158-3 |
| OBSOLETE | 3 | NO | 207158-2 |
| | 3 | YES | -207158-1 |
| CONTACT FINISH | | MOUNTING TABS | PART NO |
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN 03/10/92 L.SIPE CHK 3-17-92 R.STONE APVD 3-17-92 A.TRAVIS PRODUCT SPEC 108-10033 APPLICATION SPEC | |
| DIMENSIONS: mm [INCHES] | | NAME | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | SIZE CAGE CODE DRAWING NO RESTRICTED TO | |
| 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± - | | A2 00779 C=207158 | |
| MATERIAL | | WEIGHT - | |
| FINISH | | SCALE 4:1 SHEET 1 of 1 REV Z | |
| CONTACT: SEE TABLE | | CUSTOMER DRAWING | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-207158-0](#)