




| REVISIONS |     |               |           |     |      |
|-----------|-----|---------------|-----------|-----|------|
| P         | LYR | DESCRIPTION   | DATE      | DWN | APVD |
|           | A1  | ECR-13-012661 | 08AUG2013 | TD  | TD   |
|           | A2  | ECO-15-016378 | 12NOV2015 | DS  | YS   |
|           |     |               |           |     |      |
|           |     |               |           |     |      |

|               |   |             |
|---------------|---|-------------|
| SILVER        | F | 1-2103247-6 |
| SILVER        | E | 1-2103247-5 |
| SILVER        | D | 1-2103247-4 |
| SILVER        | B | 1-2103247-2 |
| SILVER        | A | 1-2103247-1 |
| TIN           | F | 2103247-6   |
| TIN           | E | 2103247-5   |
| TIN           | D | 2103247-4   |
| TIN           | B | 2103247-2   |
| TIN           | A | 2103247-1   |
| SHIELD FINISH |   | INDEX       |
|               |   | PART NO     |

|                                        |                                        |                           |                                                                   |     |
|----------------------------------------|----------------------------------------|---------------------------|-------------------------------------------------------------------|-----|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |                                        | DWN A DECHAZAL ZOMAR2012  | TE Connectivity                                                   |     |
| DIMENSIONS:                            |                                        | CHK A DECHAZAL ZOMAR2012  |                                                                   |     |
| mm                                     | TOLERANCES UNLESS OTHERWISE SPECIFIED: | APVD A DECHAZAL ZOMAR2012 | NAME SPLIT HEADER ASSY, HVA 280 2P W/HVIL - PLASTIC CHART DRAWING |     |
|                                        | 0 PLC ±0.50                            | PRODUCT SPEC              | SIZE CAGE CODE DRAWING NO                                         |     |
|                                        | 1 PLC ±0.50                            | APPLICATION SPEC          |                                                                   |     |
|                                        | 2 PLC ±0.15                            | WEIGHT                    | A100779C=2103247                                                  |     |
|                                        | 3 PLC ±0.05                            | CUSTOMER DRAWING          |                                                                   |     |
| MATERIAL                               | FINISH                                 | SCALE                     | SHEET                                                             | REV |
| -                                      | -                                      | 2:1                       | 1                                                                 | A2  |
| -                                      | -                                      |                           | 2                                                                 |     |

| REVISIONS |     |             |      |     |      |
|-----------|-----|-------------|------|-----|------|
| #         | LYR | DESCRIPTION | DATE | DWN | APVD |
| -         | -   | SEE SHEET 1 | -    | -   | -    |
|           |     |             |      |     |      |
|           |     |             |      |     |      |
|           |     |             |      |     |      |

|                                | X-2103247-1 (KEY A) | X-2103247-2 (KEY B) | X-2103247-4 (KEY D) | X-2103247-5 (KEY E) | X-2103247-6 (KEY F) |
|--------------------------------|---------------------|---------------------|---------------------|---------------------|---------------------|
| FRONT VIEW                     |                     |                     |                     |                     |                     |
| SIDE VIEW                      |                     |                     |                     |                     |                     |
| REAR VIEW                      |                     |                     |                     |                     |                     |
| INTERFACE VIEW - MOUNTING SIDE |                     |                     |                     |                     |                     |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.50

1 PLC ±0.50

2 PLC ±0.15

3 PLC ±0.05

4 PLC ±

ANGLES ±3

FINISH

MATERIAL

-

DWN A DECHAZAL ZOMAR2012

CHK A DECHAZAL ZOMAR2012

APVD A DECHAZAL ZOMAR2012

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME SPLIT HEADER ASSY, HVA 280 2P W/HVIL - PLASTIC CHART DRAWING

SIZE A1

CAGE CODE 00779

DRAWING NO C=2103247

RESTRICTED TO

TE Connectivity

SCALE 2:1

SHEET 2 OF 2

REV A2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2103247-1](#)