




REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-13-012661	08AUG2013	TD	TD
	A2	ECO-15-016378	12NOV2015	DS	YS

I.D. HOLES ON THESE TWO BEAMS ON SILVER SHIELD



1-2103247-X
(SILVER SHIELD)

2103247-X
(TIN SHIELD)

3 Ø8.70 MAX
FASTENER HEAD
DIAMETER FOR
MATING PLUG
CLEARANCE
(4 PLACES)



0.8 MAX WASHER/FASTENER HEIGHT
OUTSIDE OF 8.7MM MAX FASTENER DIAMETER
FOR MATING PLUG CLEARANCE




1 IDENTIFICATION MARKING ON THIS SURFACE
CONTAINS ASSEMBLY P/N AND DATE CODE (YYDDD).
TEXT ORIENTATION, SIZE, AND LOCATION CAN VARY AS LONG
AS TEXT IS ON SURFACE SHOWN AND READABLE.

2 SHIELD SEAM CAN BE POSITIONED AS SHOWN OR ROTATED
180° FROM POSITION SHOWN.

3 THESE DIMENSIONS DEFINE FASTENER SIZE LIMITS FOR
PROPER COMPONENT FUNCTIONALITY. END USER MUST ENSURE
FASTENER AND/OR WASHER DIAMETER IS 8.6 MM MIN FOR
PROPER RETENTION. THESE ARE NOT PRODUCT FEATURES -
NO INSPECTION REQUIRED FOR THESE ITEMS.

4 SURFACE FINISH APPLIES IN THIS AREA

5 NOTE DELETED



MOUNTING INTERFACE SPECIFICATION
3.0 MINIMUM MOUNTING THICKNESS
(KEY A MOUNTING INTERFACE SHOWN -
REFER TO TABLE FOR KEY B - F MOUNTING DIFFERENCES)
SCALE 2:1

SILVER	F	1-2103247-6
SILVER	E	1-2103247-5
SILVER	D	1-2103247-4
SILVER	B	1-2103247-2
SILVER	A	1-2103247-1
TIN	F	2103247-6
TIN	E	2103247-5
TIN	D	2103247-4
TIN	B	2103247-2
TIN	A	2103247-1
SHIELD FINISH		INDEX
		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A DECHAZAL CHK A DECHAZAL APVD A DECHAZAL	ZOMAR2012 ZOMAR2012 ZOMAR2012
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		0 PLC ±0.50 1 PLC ±0.50 2 PLC ±0.15 3 PLC ±0.05 4 PLC ± ANGLES ±3	
MATERIAL		WEIGHT	
-		-	
-		CUSTOMER DRAWING	
NAME		SPLIT HEADER ASSY, HVA 280 2P W/HVIL - PLASTIC CHART DRAWING	
SIZE		CAGE CODE DRAWING NO	
A1		00779C=2103247	
SCALE		2:1	
SHEET		1 OF 2	
REV		A2	

REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

	X-2103247-1 (KEY A)	X-2103247-2 (KEY B)	X-2103247-4 (KEY D)	X-2103247-5 (KEY E)	X-2103247-6 (KEY F)
FRONT VIEW					
SIDE VIEW					
REAR VIEW					
INTERFACE VIEW - MOUNTING SIDE					
	KEY A MOUNTING INTERFACE	KEY B MOUNTING INTERFACE	KEY D MOUNTING INTERFACE	KEY E MOUNTING INTERFACE	KEY F MOUNTING INTERFACE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.50

1 PLC ±0.50

2 PLC ±0.15

3 PLC ±0.05

4 PLC ±

ANGLES ±3

FINISH

-

OWN

A. DEHAZAL

ZOMAR2012

CHK

A. DEHAZAL

ZOMAR2012

APVD

A. DEHAZAL

ZOMAR2012

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

NAME

SPLIT HEADER ASSY, HVA 280 2P

W/HVIL - PLASTIC

CHART DRAWING

SIZE

A1

CAGE CODE

00779

DRAWING NO

C=2103247

RESTRICTED TO

-

TE Connectivity

SCALE

2:1

SHEET

2

OF

2

REV

A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2103247-5](#)