




2.40	2.60 2.20	1.55	1.96 1.57	1.30 - 1.60	22-24 AWG	ON REEL	6	1-2106123-6
2.40	2.60 2.20	1.55	1.96 1.57	1.30 - 1.60	22-24 AWG	ON REEL	4	1-2106123-3
2.40	2.60 2.20	1.55	1.96 1.57	1.30 - 1.60	22-24 AWG	LOOSE PIECE	2 3	1-2106123-2
2.40	2.60 2.20	1.55	1.96 1.57	1.30 - 1.60	22-24 AWG	ON REEL	2 3	1-2106123-1
3.01	2.80 2.40	2.05	2.32 1.92	1.70 - 2.10	18-20 AWG	ON REEL	4	2106123-3
3.01	2.80 2.40	2.05	2.32 1.92	1.70 - 2.10	18-20 AWG	LOOSE PIECE	2 3	2106123-2
3.01	2.80 2.40	2.05	2.32 1.92	1.70 - 2.10	18-20 AWG	ON REEL	2 3	2106123-1
DIM D	DIM C	DIM B	DIM A	INSULATION DIA	WIRE RANGE	REMARKS	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN R. BROWN 04MAR2009	TE Connectivity			
				CHK A. BUCHER 04MAR2009				
DIMENSIONS: mm				APVD -	NAME			
				PRODUCT SPEC	CONTACT, RECEPTACLE, CRIMP SNAP-IN SLIM SEAL SSL			
				108-2391				
MATERIAL				APPLICATION SPEC	SIZE			
				114-13261				
				WEIGHT	CAGE CODE			
				-				
SEE TABLE				CUSTOMER DRAWING	DRAWING NO			
				SCALE 10:1	RESTRICTED TO			
					SHEET 1 OF 1			
					REV A3			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2106123-1](#)