


LOC	DIST	P	F	REVISIONS			
				ZONE	LTR	DESCRIPTION	DATE
DF	AO				C	REV PER 063D-0289-00 CT	10-00

SOCKET CONTACT BODY
MAT'L: COPPER ALLOY PER MIL-C-39029
FINISH: GOLD PLATE .000050 MIN PER MIL-G-45204
OVER NICKEL PLATE .000050 MIN PER QQ-N-290

HOOD
MAT'L: STAINLESS STEEL PER QQ-S-766
FINISH: PASSIVATION PER QQ-P-35B



.522 [13.26]	1.441 [36.60]	.953 [24.21]	1-211245-2
.392 [9.96]	1.311 [33.30]	.823 [20.90]	1-211245-0
.636 [16.15]	1.555 [39.50]	1.067 [27.10]	211245-8
.500 [12.70]	1.419 [36.04]	.931 [23.65]	211245-6
.375 [9.53]	1.289 [32.74]	.801 [20.35]	211245-4
.250 [6.35]	1.169 [29.69]	.681 [17.30]	211245-2
MINIMUM EXTENSION BEYOND INSERT		B DIM REF	A DIM
			PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 [0.13] ANGLES ± - MATERIAL SEE CALLOUTS FINISH SEE CALLOUTS	DR 5-9-91 C.C.THOMAS	AMP AMP Incorporated Harrisburg, PA 17105-3608	
	CHK 6-19-91 A.SHARPE		
	APPD 6-19-91 A.SHARPE	NAME POSTED SOCKET CONTACT ASSY, NIC 600,SQUARE,SIZE 22, FRONT RELEASE	
	APPD 6-19-91 C.C.THOMAS		
	PRODUCT SPEC	SIZE	CAGE CODE
		SCALE	10:1
	WEIGHT		SHEET
			1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[211245-4](#)