

4

3

2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		H2	REVISED PER ECO-07-008008	10APR07	JDP	CWR

D

C

B



A

D


C

B

A



- 1 NYLON, UL 94V-0 RATED, BLACK.
- 2 2.54μm [.000100] MIN TIN-LEAD OVER 1.27μm [.000050] MIN NICKEL.
- 3 TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290.
- 4 ACCEPTS #2 SELF-TAPPING SCREW, .250 LONG REF.
- 5. MATES WITH 6 POSITION SHIELDED DIN PLUG 212437-4.
- 6 BRASS PER ASTM B36.
- 7 2.54μm [.000100] MIN TIN OVER 1.27μm [.000050] MIN NICKEL.



OBSOLETE	7	9-211509-0
	2	211509-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	A.STAUB BG	8/12/91	tyco Electronics			Tyco Electronics Corporation Harrisburg, PA 17105-3608		
DIMENSIONS: mm [INCHES]		CHK	-	-				NAME		
		APVD	-	-	PRODUCT SPEC			108-10047		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:			APPLICATION SPEC			114-40025		
MATERIAL		FINISH			WEIGHT			-		
1		SEE TABLE			CUSTOMER DRAWING			SIZE	CAGE CODE	DRAWING NO
								A2	00779	C=211509
								RESTRICTED TO	-	
								SCALE	4:1	SHEET 1 of 1
								REV	H2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9-211509-0](#)