



LOC		DIST		REVISIONS					
—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
					AK	REV PER ECO-15-016251	13NOV15	KG	CD

1. THIS RECEPTACLE WILL MATE WITH ANY 5C5, SIZE 3 PLUG IN AMPLIMITE SERIES.
2. USE (5) POWER 8, OR COAX SOCKET CONTACTS. CONSULT PRODUCT ENGINEERING FOR MORE DETAILS.
- 3 CADMIUM PER QQ-P-416.
- 4 FINISH: TIN PER ASTM-B-545 .000200 MIN THK OVER COPPER PER AMS2418 .000100-.000200 THK.
- 5 ALL EXCEPT FOR 212059-5 AND 212059-6.
- 6 4-40 UNC-3B CLINCH NUT, 2 REQ'D.
- 7 CUSTOMER PART NO. INK STAMPED FAR SIDE.
- 8 UL/CSA DESIGNATION STAMPED IN THIS AREA, OPTIONAL.
- 9 STEEL PER ASTM-A-109.
- 10 BRASS PER ASTM-B-36.
- 11 GOLD PLATED PER MIL-G-45204 OVER COPPER PER AMS2418.
- 12 FINISH: TIN PER ASTM-B-545 .000400 MIN THK OVER COPPER PER AMS2418 .000050 MIN THK.
- 13 ZINC PLATE PER ASTM-B-633, .000200-.000400 THK WITH SUPPLEMENTARY CHROMATE (Cr3+)





CLINCH NUT #4-40UNC
2 REQ'D
MAT'L: CARBON STEEL
FINISH: PLATED ZINC
YELLOW CHROMATE
212059-5 ONLY



-	56912	5-212059-5
-	913	5-212059-1
B010942-0008	71011	1-212059-3
B010942-0007	71011	1-212059-1
-	912	1-212059-0
-	912	212059-9
-	-	212059-8
B010942-0016	71011	212059-7
311P405-10S-B-15	71011	212059-6
-	4569	212059-5
97942-645A935H01	379	212059-4
-	49	212059-3
311P405-10S-B-12	71011	212059-2
-	39	212059-1
CUSTOMER PART NO	REMARKS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SHUEY 14JAN88	 TE Connectivity	
DIMENSIONS: INCHES		CHK A. EMADI 26JAN88		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	RECEPTACLE ASSEMBLY AMPLIMITE 5C5 SERIES 109, SIZE 3, COAX MIX	
	0 PLC ± -	PRODUCT SPEC		
	1 PLC ± -	APPLICATION SPEC		
	2 PLC ± -	SIZE		
MATERIAL	3 PLC ± .005	WEIGHT	A100779C=212059	
	4 PLC ± -	CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV AK	
FINISH				



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[212059-1](#)