



LOC	DIST	P	F	REVISIONS			
				ZONE	LTR	DESCRIPTION	DATE
DF	BO				C	REV & REDRAWN DF-4297	PY 11-91
					D	REV PER 0600-4161-95 JB	08-30-95



- 1 MATERIAL: DIALLYL PHTHALATE PER MIL-M-14,TYPE SDG-F,COLOR-BLUE
- 2 AMP PART NO AND DATE CODE AND ARROWS MARKED WITH WHITE INK OR BY LASER MARKING AT APPROX AREA SHOWN
- 3 WARNING STATEMENT MARKED WITH WHITE INK AT APPROX AREA SHOWN
4. THIS MODULE ACCEPTS MINIATURE COAXICON AND TYPE I-SIZE 12 PIN CONTACTS

CAVITY CONFIGURATION PER VIEW A	213090-4
ALL CAVITIES IDENTICAL TO CAVITY 3	213090-2
DESCRIPTION	PART NUMBER



DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± -		DR 7-16-91 P.YEAGER CHK 11-12-91 D.B.MUMMEY APPD 11-12-91 D.B.MUMMEY APPD - PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME MALE BLOCK 8 POSN,G SERIES SIZE CAGE CODE DRAWING NO 00779 213090 SCALE 4:1 SHEET 1 OF 1		
MATERIAL 1		FINISH -				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[213090-4](#)