









REVISIONS					
P.	LTR	DESCRIPTION	DATE	DWN	APVD
	D4	REVISED PER ECR-17-014071	30DEC2017	W, H	D, Z






- 1 MATERIAL: HOUSING:HIGH PERFORMANCE RESIN,UL94V-0,NATURAL.
CONTACT: BRASS, NICKEL UNDER PLATING,
TIN PLATING ON PIN AREA.
- 2 CONTACT RETENTION: 20 NEWTON [4.5 lbf] MIN.
- 3 CONTACT SOLDERTAIL KINK DIRECTION SEE BELOW TABLE.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 06JAN11	 TE Connectivity								
DIMENSIONS: mm[INCHES]		CHK MACE SAMUEL 06JAN11									
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD MACE SAMUEL 06JAN11	NAME HEADER ASSEMBLY, VERTICAL, ECONOMY POWER, 2.5mm CENTERLINE	SIZE A	CAGE CODE 00779	DRAWING NO C-2132415	RESTRICTED TO -				
		PRODUCT SPEC 108-2418									
		APPLICATION SPEC 114-13315									
		WEIGHT -									
		CUSTOMER DRAWING						SCALE 6:1	SHEET 1 OF 2	REV D4	
		MATERIAL -									
FINISH -											
1 P/LC ±0.50 1 P/LC ±0.30 2 P/LC ±0.20 3 P/LC ±0.10 4 P/LC ±0.05 ANGLES ±°											

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



47.50[1.870]	50.83[2.001]	52.50[2.067]	20	2-2132415-0
45.00[1.772]	48.33[1.903]	50.00[1.968]	19	1-2132415-9
42.50[1.673]	45.83[1.804]	47.50[1.870]	18	1-2132415-8
40.00[1.575]	43.33[1.706]	45.00[1.772]	17	1-2132415-7
37.50[1.476]	40.83[1.607]	42.50[1.673]	16	1-2132415-6
35.00[1.378]	38.33[1.510]	40.00[1.575]	15	1-2132415-5
32.50[1.280]	35.83[1.411]	37.50[1.476]	14	1-2132415-4
30.00[1.181]	33.33[1.312]	35.00[1.378]	13	1-2132415-3
27.50[1.083]	30.83[1.214]	32.50[1.280]	12	1-2132415-2
25.00[.984]	28.33[1.115]	30.00[1.181]	11	1-2132415-1
22.50[.886]	25.83[1.016]	27.50[1.083]	10	1-2132415-0
20.00[.787]	23.33[.919]	25.00[.984]	9	2132415-9
17.50[.689]	20.83[.820]	22.50[.886]	8	2132415-8
15.00[.591]	18.33[.722]	20.00[.787]	7	2132415-7
12.50[.492]	15.83[.623]	17.50[.689]	6	2132415-6
10.00[.395]	13.33[.525]	15.00[.591]	5	2132415-5
7.50[.295]	10.83[.426]	12.50[.492]	4	2132415-4
5.00[.197]	8.33[.328]	10.00[.395]	3	2132415-3
2.50[.098]	5.83[.229]	7.50[.295]	2	2132415-2
DIM C	DIM B	DIM A	POS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA	06JAN11	 TE Connectivity		
		CHK MACE SAMUEL	06JAN11			
DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD MACE SAMUEL	06JAN11	NAME	HEADER ASSEMBLY, VERTICAL, ECONOMY POWER, 2.5mm CENTERLINE	
		PRODUCT SPEC 108-2418				
	0 PLC ±0.50 1 PLC ±0.30 2 PLC ±0.20 3 PLC ±0.10 4 PLC ± ANGLES FINISH	APPLICATION SPEC 114-13315		SIZE	CAGE CODE A100779	
		WEIGHT -				DRAWING NO C=2132415
MATERIAL -		CUSTOMER DRAWING		SCALE 6:1	SHEET 2 OF 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2132415-8](#)