


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		D	REVISED PER 0G3B-0008-04	1/12/04	SS	GS



- 1

BERYLLIUM COPPER.
- 2

PHOSPHOR BRONZE.
- 3

0.76μm [.000030] MIN GOLD OVER 1.27μm [.000050] MIN NICKEL.
- 4

2.54μm [.000100] MIN NICKEL.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 2-5-92		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105	
		CHK R.STONE 2-7-92			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SOCKET CONTACT ASSEMBLY, #10 AWG, POWER VIII, METRIMATE —	
		APVD —			
		PRODUCT SPEC 108-1317			
		APPLICATION SPEC 114-10014			
		WEIGHT —			
		CUSTOMER DRAWING			
MATERIAL		FINISH		SIZE A2	
SOCKET CONTACT: ①		SOCKET CONTACT: ③		CAGE CODE 00779	
RETAINING RING: ②		RETAINING RING: ④		DRAWING NO G=213737	
				RESTRICTED TO —	
				SCALE 10:1	
				SHEET 1 OF 1	
				REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[213737-1](#)