







LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
H	—	N		EH-1637-99	02-11-98	MVE —
		P		ECR-06-013127	31-05-06	MO —
		P1		ECR-08-012368	05-11-08	AEG WRV
		P2		REVISED PER ECO-09-020935	29AUG09	KK AEG

- NOTES:
- FOR APPLICATION INFORMATION SEE
TE SPECIFICATION 114-19005.
 - FOR PERFORMANCE REQUIREMENTS SEE
TE SPECIFICATION 108-19039.
 - OBSELETE PARTS: OBSELETE CIS STREAMLINING PER D.RENAUD/D.SINISI



MATERIALS OF CONTACTS:
PHOS. BRONZE.

OBSOLETE	800 PCS ON TAPE	0.8 μm	ABS COLOR-CLEAR	2-215222-4
	3000 PCS IN A BOX			215222-4
	800 PCS ON TAPE			2-215222-3
	3000 PCS IN A BOX	1.25 μm	PBT, UL 94V-0 COLOR-BLACK	<div>3</div> 215222-3
				215222-1
	PACKAGING	GOLD PLATING IN CONTACT AREA	HOUSING MATERIAL	ORDER NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BEJNON CHK — APVD — PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		24APR89		 Tyco Electronics Corporation 's-Hertogenbosch, Nederland							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		MODULAR JACK M.T., 4 POS./4 CONT WITH INSULATION DISPLACEMENT CONTACTS							
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		—		SIZE A2		CAGE CODE 00779		DRAWING NO C-215222		RESTRICTED TO —	
MATERIAL SEE NOTES		SEE NOTES		CUSTOMER DRAWING		SCALE NTS		SHEET 1 of 1		REV P2			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[215222-1](#)