







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		R	EH-1477-98	14-09-98	EVE	—
			R1	ECR-08-012368	06-11-08	AEG	WRV
			R2	ECR-10-022530	07JAN11	KK	HMR

NOTES:

1. TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0,15$.
2. MODULAR JACK P.N. 216446-1, 216446-2, 3-216446-1 AND 3-216446-2 ARE DELIVERED WITH PLASTIC SOLDER STOP INSTALLED, TO PREVENT SOLDER ENTERING THE JACK. REMOVE SOLDER STOP AFTER SOLDERING.
3. FOR PERFORMANCE REQUIREMENTS SEE TE PRODUCT SPECIFICATION 108-19064.
4. FOR APPLICATION REQUIREMENTS SEE TE APPLICATION SPECIFICATION 114-19019.
5. MOLDED-IN CHARACTER "1,6" MEANS FOR 1,6mm PRINT THICKNESS.
6. FOR PACKAGING SEE SHEET 2.
7. PREFERRED DIRECTION FOR STAMPING OF HOLE TO OBTAIN A BROKEN EDGE AT JACK ENTRY SIDE.
8. TRUE POSITIONING OF THE SOLDER TINES MAY BE AFFECTED BY BULK PACKAGING. THE SOLDER STOP COULD BE LOOSENED DURING TRANSPORT.



OBSOLETE		BULK PACKAGED 500 pcs/BOX	6 POS./4 CONTACTS WITH SOLDER STOP	CONTACTS: 1,25µm MIN. GOLD OVER	HOUSING: 20% G.F. NYLON	3-216446-2
		BULK PACKAGED 1000 pcs/BOX	6 POS./6 CONTACTS WITH SOLDER STOP	1,25µm MIN. NICKEL IN CONTACT AREA	COLOR: BLACK UL 94-HB	3-216446-1
		700 pcs ON A .60 cm DIA REEL	6 POS./4 CONTACTS WITH SOLDER STOP	2µm MIN. TIN LEAD OVER 1,25µm MIN.	CONTACTS: PHOS. BRONZE	216446-2
		700 pcs ON A ø60 cm DIA. REEL	6 POS./6 CONTACTS WITH SOLDER STOP	NICKEL ON SOLDER TINES.		216446-1
		DESCRIPTION		FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.V.ESSSEN	29NOV95	 TE Connectivity			
DIMENSIONS: mm		CHK W.BRUMMANS	—				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	APVD C.V.TILBURG	—	NAME MODULAR JACK, 6 POS BOTTOM ENTRY VERSION FOR PRINTED CIRCUIT BOARD MOUNTING			
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL —	FINISH —	WEIGHT —	A2	00779	C-216446	RESTRICTED TO —	
CUSTOMER DRAWING					SCALE NTS	SHEET 1 of 2	REV R2

LOC	DIST	REVISIONS			
H	-	P	LTR	DESCRIPTION	DATE
		-		SEE SHEET 1	-

D

C

B


A

D

C

B

A



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN F.V.EIJK	19DEC96	TE Connectivity	
DIMENSIONS: mm		CHK W.BRUMMANS	-		
		APVD R.SMEETS	-	NAME	
		PRODUCT SPEC	-	MODULAR JACK, 6 POS., BOTTOM ENTRY VERSION PACKAGING	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	-	SIZE	CAGE CODE
0 PLC ± -		WEIGHT	-	A2	00779
1 PLC ± -		CUSTOMER DRAWING		DRAWING NO	
2 PLC ± -		SCALE		SHEET	
3 PLC ± -		NTS		2 OF 2	
4 PLC ± -		REV		R2	
ANGLES ± -		RESTRICTED TO		-	
FINISH		C=216446		-	
MATERIAL		-		-	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-216446-2](#)