

NOTES:



- 1

CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1,27 CENTERS.
FOR CABLE REQUIREMENTS SEE APPLICATION SPECIFICATION 114-19022.
- 2

INDICATION OF FIRST CABLE POSITION REFERRING TO CORRESPONDING
CONTACT POSITION (BLACK INK MARKS)
- 3

SOLDER-TINES FOR 0,8^{±0,05} DIA. HOLES.
- 4

PRODUCT SPECIFICATION 108-19033



						③ CONTACTS			PHOSPHORBRONZE		3, 0-5, 1µm TIN WITH ENTIRE NICKEL UNDERCOATING						
OBSOLETE	86, 36	78, 74	64	6-216791-4	B	② HOUSING AND COVER			THERMOPLASTIC POLYESTER		GREY						
	81, 28	73, 66	60	6-216791-0	B	① HOUSING											
	68, 58	60, 96	50	5-216791-0	B	COMPONENT NAME			MATERIAL		PLATING / COLOUR						
	60, 96	53, 34	44	4-216791-4	B	—	—	—	CUSTOMER DRAWING			FOR REFERENCE ONLY WILL NOT BE UPDATED					
	55, 88	48, 26	40	4-216791-0	B	—	—	—	C COPYRIGHT 19- BY TE HOLLAND B. V. ALL INTERNATIONAL RIGHTS RESERVED. TE PRODUCTS MAY BE COVERED BY U. S. AND FOREIGN AND/OR PATENTS PENDING.								
	48, 26	40, 64	34	3-216791-4	B	—	—	—	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION , 19								
	38, 10	30, 48	26	2-216791-6	B	B3	ECR-10-022530		KK	HMR	07JAN11	 TE Connectivity					
	30, 48	22, 86	20	2-216791-0	B	B2	ET00-0243-04		A. V.	C. T.	21MAR2005						
	25, 40	17, 78	16	1-216791-6	B	B1	ET00-0023-04		D. C.	C. T.	09FEB2004						
	22, 86	15, 24	14	1-216791-4	B	B	H-9670		JvdH	R. V.	20-03-92						
	17, 78	10, 16	10	1-216791-0	B	LTR.	REVISION RECORD		DR.	CHK.	DATE						
	12, 70	5, 08	6	216791-6	B	DR. : R. HOGVEEN.		CHK. : R. VERSTIJNEN.		APP. : L. V. SOEST.		DWG. No.		REV. LTR.		SHEET	
		DIM. " B" REF.	DIM. " A" REF.	NR. OF POS.	PARTNUMBER	PART REV.	DATE: 06-11-89		DATE: 09-11-89		DATE: 09-11-89		C-216791		B3		1 OF 1
A3																	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-216791-0](#)