




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE	08NOV2016	JY	SH

D





1. COMPONENTS
CAGE ASSEMBLY: NICKEL-SILVER ALLOY
HEAT SINK: ALUMINUM/BLACK ANODIZE
HEAT SINK CLIP: STAINLESS STEEL
EMI SPRING: COPPER ALLOY/NICKEL PLATE
LIGHT PIPE: CLEAR POLYCARBONATE WITH UL 94 V-0
ORGANIZER: POLYESTER WITH UL 94 V-0
EMI GASKET: PLATED FILLED SILICONE
2. REFERENCE APPLICATION SPECIFICATION 114-32023 FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS
3. DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER
4. MATES WITH QSFP28 MSA COMPATIBLE TRANSCEIVER.
5. LIGHT PIPES ARE SHIPPED ASSEMBLED ON CAGE
6. MINIMUM PC BOARD THICKNESS: SINGLE SIDED: 1.57 MIN
DOUBLE SIDED: 3.00 MIN
7. DATUM **-A-** IS TOP SURFACE OF THE HOST BOARD.
8. THESE HOLES ARE OPTIONAL WHEN THE REAR PINS ARE REMOVED.
9. DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN.

C





B



WITHOUT	2170784-2
WITH	2170784-1
REAR PINS OPTIONAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26JAN2014 JASON YANG	 TE Connectivity			
		CHK 08NOV2016 SEAN HAN				
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.25 2 PLC ±0.2 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH	APVD -	NAME RECEPTACLE CAGE ASSEMBLY 1X4, QSFP28 WITH LIGHT PIPES THRU BEZEL, GASKET			
		PRODUCT SPEC 108-19428				
MATERIAL SEE NOTES -	SEE NOTES -	APPLICATION SPEC 11-32023	SIZE A2	CAGE CODE 00779	DRAWING NO C-2170784	RESTRICTED TO -
		WEIGHT -	CUSTOMER DRAWING			SCALE 3:1

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 26 JAN 2014
JASON YANG

CHK 08 NOV 2016
SEAN HAN

APVD -

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.25

2 PLC ±0.2

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

PRODUCT SPEC

108-19428

APPLICATION SPEC

11-32023

WEIGHT

-

CUSTOMER DRAWING

NAME

RECEPTACLE CAGE ASSEMBLY
1X4, QSFP28 WITH LIGHT PIPES
THRU BEZEL, GASKET

SIZE

A2

CAGE CODE

00779

DRAWING NO

C-2170784

RESTRICTED TO

-

SCALE

3:1

SHEET


2 OF 5

REV

A




RESTRICTED TO
—
REV A



THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20	
COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26 JAN 2014 JASON YANG	TE Connectivity		
		CHK 08 NOV 2016 SEAN HAN			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ± 1 PLC ±0.25 2 PLC ±0.2 3 PLC ± 4 PLC ±		PRODUCT SPEC	
		ANGLES ±		APPLICATION SPEC	
FINISH		SEE NOTES		SIZE	
MATERIAL		SEE NOTES		CAGE CODE	
SEE NOTES		SEE NOTES		DRAWING NO	
				RESTRICTED TO	
				A200779C-2170784	
				SCALE 3:1	
				SHEET 4 OF 5	
				REV A	



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JASON YANG 26 JAN 2014	TE Connectivity		
DIMENSIONS: mm		CHK SEAN HAN 08 NOV 2016			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.25 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ± FINISH		APVD - PRODUCT SPEC 108-19428 APPLICATION SPEC 11-32023 WEIGHT - CUSTOMER DRAWING	NAME RECEPTACLE CAGE ASSEMBLY 1X4, QSFP28 WITH LIGHT PIPES THRU BEZEL, GASKET		
MATERIAL SEE NOTES		SCALE 3:1	SIZE A200779	DRAWING NO C-2170784	RESTRICTED TO -
SEE NOTES		SHEET 5 OF 5	REV A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2170784-1](#)