






P	LYR	NEW RELEASE	01DEC2014	CR	JK
	A	ECR-20-005122	08APR2020	BP	CW



TECHNICAL DATA	4-2172082-2
RATED VOLTAGE	125V
RATED IMPULSE VOLTAGE	1500V
POLLUTION DEGREE	3
OVERVOLTAGE CATEGORY	II
MATERIAL GROUP	II
RATED CURRENT	4A
VOLUME RESISTIVITY	≤ 3mΩ
DEGREE OF PROTECTION	IP67
UPPER TEMPERATURE	+85 °C
LOWER TEMPERATURE	+40 °C




ITEM	DESCRIPTION	MATERIAL	COMMENT
1	SHELL	CuZn	NICKEL PLATED
2	NUT	CuZn	NICKEL PLATED
3	O-RING	RUBBER	-
4	PLASTIC BODY	PA	-
5	CONTACT	CuZn	AU PLATED

NOTE:

1.THE COMPONENTS ITEM NO 1, 2, 3 ARE PACKAGE AS A SEPERATE HARDWARE.

2.ALL DIMENSIONS ARE FOR NOMINAL REFERENCE ONLY UNLESS OTHERWISE STATED.

		5		4-2172082-2	
		NUMBER OF POLES		TE-PART-NO.	
DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).					
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		DWN 12SEP2014 YASHKUMAR		 TE Connectivity	
		CHK 12SEP2014 M. BRUBAKER			
		APVD 12SEP2014 M. BRUBAKER			
DIMENSIONS: MASSE/INSEITEN: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLE GEMÄSS TOLERANZEN		NAME M12 MALE CONNECTOR, PCB ASSEMBLY, ANGLED, UNSHIELDED, B-CODED	
		PRODUCT SPEC PRODUKTSPEZ. 108-19483			
		APPLICATION SPEC VERARBEITUNGSSPEZ. 114-32127			
		WEIGHT GEWICHT -			
		MATERIAL - -			
		FINISH/ÖBERFLÄCHE/FARBE		RESTRICTED TO NUR FÜR -	
		Customer Drawing		/KUNDENZEICHNUNG	
		SCALE MASSSTAB		SHEET BLATT	
		2:1		OF VON	
		1		REV A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2172082-2](#)